

OverView fPR67-DL

67" Display Wall system integrating 3-panel Poly-Silicon LCD technology with SXGA resolution.
Includes front access and dual lamp.



技術仕様

OVERVIEW FPR67-DL

一般仕様	
解像度	SXGA
アスペクト比	5:4
カラー	16.7 millions
ランプ	• Dual lamp • 2 x 100 W • Operation time 2 x 8000 h (average) • 100% availability of display wall • Keeps track of the 2 lamp life times • Detects lamp failure • When switching from one lamp to the other, constant display quality is offered • 3 modes: Hot Stand-By: 2nd lamp is on so that the switching time in case of lamp failure of the master lamp is minimal Cold Stand-By: 2nd lamp is switched off during operation, will only be activated when a lamp failure is detected of the master lamp Auto Switch Mode: regularly switch every 500 hours
電源	100-240 VAC, 50-60 HZ
電力	• 330 W in hot standby • 220 W in cold standby
輝度	110 cd/m ² 32 fL
輝度	500 lumens
コントラスト	350:1
輝度均一性	>95 %
寸法ストラクチャ	• Diagonal 67" • Width 1335 mm / 52.56 in. • Height 1068 mm / 42.05 in. • Footprint 690 mm / 27.17 in. • Depth 822 mm / 32.36 in. • Socket heigth (min) 606 mm / 23.86 in. • Socket heigth (max) 1288 mm / 50.71 in • Weight 133 kg / 239 lbs
環境準拠	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity 40%-60%, non condensing
フロント・アクセス	• To engine, both lamps & filters • No limitations to install the system against a back wall
スクリーン	Black type screen with large viewing angles Download the brochure for more info on the principles and technologies

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

