

SP4K-40B

40,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPureTM**
- **Fit and forget**

SP4K-40B is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A 4K RGB projector family, designed for cinema. The SP4K models come in many different configurations offering you the freedom of choice. A range of lumens, compatibility with both Barco lenses and selected 3rd party lenses, and optional touch displays. Play with the available options to match your specific needs.

Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image ManagementTM and its patented precision brightness technology guarantees flawless images with automatic white balances.

Ready for tomorrow, today

The Barco ColorgenicTM technology opens up the full P3 color space and more than 98.5% of Rec. 2020. SP4K-40B is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

Barco EcoPureTM

This silent running projector (51dB(A)) is fully ready for boothless operation. In addition, the SP4K-40B smartly manages its power consumption resulting in a high projector efficiency of 10.3 lm/W. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plateTM spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-40B seamlessly integrates into your current setup.

Product specifications**SP4K-40B****General specifications**

Native brightness	40,000 lumens (typical)
Native contrast ratio	2000:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 1.38" DC4K
Resolution	native 4K: 4096 x 2160
Color gamut	DCI P3 (98.5% of Rec. 2020; when measured in xy-color coordinates)
Light source	Laser
Prime lenses	1.13-172; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98 High-brightness and high-contrast B-lenses compatible
Long-term brightness stability	40,000 hrs @ average usage conditions
Housing	integrated cooling design and patented sealed optical assembly
Dimensions (WxLxH)	projector incl. feet 760 x 1470 x 612 mm 29,92 x 57,54 x 24,09 inches
Weight	170kg/375lbs
Power requirements	single phase or triple phase 200-240V 25A
Heat load (max. power)	12,500 BTU/hr
Exhaust airflow	615CFM
Ambient temperature	40°C / 104F max.
Ambient humidity	85% RH max.
Media server	Barco Alchemy ICMP-X and other media server brands ** supported
Power consumption	3.9kW (3W in Eco mode)
Noise Level	51dB(A) @1m and 25°C ambient temperature
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Safety requirements	Class 1 risk group 3
User interface	Touch Display and/or web based
Notes	** projector configuration with ICP-D; contact Barco service for the list of supported brands

Last updated: 04 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.