

BarcoGraphics 6300



- High light output of 2,200 ANSI lumen
- Native panel resolution of 1,024 x 768 pixels
- Vibrant images with remarkable depth and clarity
- Perfect geometry
- Razor sharp in every corner
- Exceptional input compatibility
- Impressive array of input connections
- Easy picture alignment through BARCO's AutoImage feature
- Direct stacking
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement for older generation projectors

Technische Daten**BARCOGRAPHICS 6300****Allgemeine technische Daten**

Lichtausgabe	2200 ANSI Lumen
LCD-Panels	3 active matrix poly-silicon LCD panels (1.8" diagonal) with a resolution of 1,024 x 768 pixels (aspect ratio 4:3)
Kompatibilität	All current Video sources in Composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic workstations with a resolution up to 1280 x 1024 pixels/60 Hz Most sources with a pixel clock up to 135 MHz
Kontrast	>350:1 (full white/full black)
Lampe	400 Watt metal-halide arc lamp with a typical lifetime of 750 hours
Bildgröße	For the zoom lenses : 1 -6 m For the 0.8 lens : 1 -1.7 m
Gewicht	Body only: 17.7 kg / 39.0 lbs. Body + lens: 21 -25 kg / 46.3 -55.1 lbs.

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.

www.barco.com

BARCO