

BarcoReality 6400



- Extremely high light output of 3400 ANSI lumen
- Three active matrix 1.8" S-XGA Poly-Silicon LCD panels with Micro Lens Array (MLA) and a resolution of 1280 x 1024 pixels
- BARCO's advanced True Color Reproduction feature processes conventional video signals and transforms them into brilliant images with vibrant colors and amazing color depth
- BARCO's patented Pixel Map Processor guarantees very legible characters and the greatest amount of picture detail possible
- Unmatched input compatibility with all analog and digital video sources and all computer graphics formats and electronic workstations up to 2,000 x 1,280 pixels
- Easy picture alignment
- Direct stacking
- Easy lamp and lens replacement
- Auto-source recognition and configuration
- Motorized zoom, focus and lens shift
- Precise projection from any position or distance
- Easy replacement of older generation projectors
- Up to 120 % off-axis projection and extra 25 % keystone correction

Product specificaties**BARCOREALITY 6400****General specifications**

Lichtuitvoer	3400 ANSI Lumen
Lcd-panelen	3 active matrix 1.8" diagonal S-XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1280x1024 pixels (5:4 aspect ratio)
Compatibiliteit	All Current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in Composite, S-VHS, Component or RGB formats All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV,...) All computer graphics formats from VGA, S-VGA, XGA to S-XGA Most Macintosh computers Electronic Workstations with a resolution up to 2000x1280 pixels/76 Hz Most sources with a pixel clock up to 200 MHz
Contrast	> 250:1 (full white/full black) > 150:1 (5x4 checkerboard)
Lamp	A new 400 Watt metal-halide arc lamp pre-aligned for maximum light output with a typical lifetime of 1000 hours
Schermaformaat	From 1-6 m, except for the QGD (0.8:1) lenses
Gewicht	Body only: 17.7 kg/39.0 lbs. Body + lens: 21-25 kg/46.3-55.1 lbs.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO