

TransForm WSM-200

Compact universal Windows 7 workstation



- Compact form factor
- Intel (R) Core (TM) i7 quad core processor for concurrent application processing
- High-end 3D graphics acceleration
- Extremely silent operation

Barco's WSM-200 Workstation Mini is a powerful, Windows 7™ based PC, and a perfect universal platform for all types of user applications. While featuring a stylish, compact form factor, the unit includes all ingredients of a high-performance workstations.

The Intel i7 quad core processor, an NVidia professional 3D graphics card and an ultra-fast SSD drive make sure, that the Workstation Mini delivers the power needed by today's applications.

Compact and extremely silent

With the general purpose PC design, the Workstation Mini is not only the preferred controller for OBLX/OBPX video walls, but it is also suitable for many other workstation-type use cases.

The compact and extremely silent design allows placing the unit even inside the control room or meeting room.

Features

- Powerful Workstation
- Compact form factor
- Intel (R) Core (TM) i7 quad core processor for concurrent application processing
- High-end 3D graphics acceleration
- Extremely silent operation

- Mature Barco quality, robust and reliable
- Perfect integration into OBLX/OBPX display system
- Powerful Workstation
- Compact form factor
- Intel (R) Core (TM) i7 quad core processor for concurrent application processing
- High-end 3D graphics acceleration
- Extremely silent operation
- Mature Barco quality, robust and reliable
- Perfect integration into OBLX/OBPX display system

Product specifications**TRANSFORM WSM-200****General specifications**

OS	Windows 7 64 bit Ultimate
CPU	Intel Core i7 Quad Core Processor
CPU frequency	3.4 GHz (up to 3.9GHz)
Memory	8 GB RAM
Hard disk	256 GB Solid-State Disk SSD
Platforms	NGP-200
Network	2x 1Gb/s LAN
Graphics card	NVIDIA Quadro-series K2000 professional graphic card
Outputs	2x Display Port 1.2 (incl. 1x DP2DVI adapter) 1x DVI Duallink
Keyboard & mouse	USB or wireless version available -supported languages US, UK, DE, ES, BE, IT, FR -Wireless version supporting AES encryption for safe data transmission -optional USB extension 20m or 50m
Barco OBLX/OBPX compatibility	Validated for OBLX with Barco OVD/KVD displays, incl. 1x1 to 4x1, 1x2 to 4x2 setups Validated for OBPX with Barco OVD/KVD displays, incl. 1x1, 2x1, 3x1 setups
Form factor	3U ½ 19" Rackmount housing
Dimensions	133mm x 220mm x 279mm 5.24" x 8.66" x 10.98"
Power supply	100-240V, 50/60Hz
Power consumption	Max. 270W Typ. 124W
Temperature range	0° -40° C 32° -104° F
Humidity	Max. 80% (non-condensing)
Noise Level	Max. 31dbA (measured at 1m/3.28ft distance at 22°C/72°F)
Compliance	CE, CB, IEC 609501, ETL, FCC Class A, CCC, BIS
Available models	Order no. R9838208 WSM-200 Workstation Mini

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.