

iCon H600

Network-centric, 1080p HD, 6,000 lumens LCD projector



Product specificaties

ICON H600

General specifications

Lichtuitvoer	6000 ANSI lumens
Resolutie	HD 1080 (1920x1080px)
Helderheidsuniformiteit	> 95 % for the total screen
Contrastverhouding	> 800:1 (full white/full black)
Beeldscherm	3 x 1.65" polysilicon LCD panel with native HDTV resolution (1920 x 1080 pixels)
Kenmerken	■ AutoImage ■ Advanced picture-in-picture ■ Standard cable basket ■ Advanced digital zoom ■ Advanced Desktopintegration
Picture-in-Picture	Background desktop image + up to 4 sources simultaneously (data or video)
Ingangen	Standard: ■ Layer 1: RGBHV or Component input; Composite video input; S-Video input ■ Layer 2: RGBHV or Component input; Composite video input; S-Video input ■ Layer 3: DVI input and D15 input ■ Layer 4: Available for optional inputs Optional: The following input boards can be placed on any of the 4 layers: ■ RGBHV or Component input; Composite video input; S-Video input ■ DVI input and D15 input ■ SDI and HDSDI input and loop trough
Uitgangen	DVI out (1920 x 1080 at 60 Hz) of full screen composed image (including window inserts)
Communicatie	■ 1x RS-232C (D-9 connector) ■ mini-jack for wired remote control
Compatibiliteit	■ All current video sources ■ All current HDTV sources ■ All computer graphics sources with a pixel clock up to 275 Mhz (VGA, XGA, SXGA, SXGA+, UXGA, QXGA: 2048x1536) ■ DVI up to UXGA and HDTV resolution ■ HD-SDI, SDI optionally available
Compatibiliteit invoerbron	2048 x 1536 @ 56Hz max input
Scherfmaat	From 1-6m / 3-20ft
Scanfrequenties	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
Netwerkverbinding	2 x 10/100/1000 Base-T Ethernet
Geïntegreerde beeldschermserver	■ Provides native 1920 x 1080 resolution ■ Pentium 4 2.6 Ghz, 1 Gigabyte DDR RAM, 40 Gigabyte harddisk (upgradeable) ■ 2 x PCMCIA slot for Wireless LAN cards, memory cards, extensions for inputs and outputs, Bluetooth ■ 2 USB connectors and PS2 connector ■ 2 x 10/100 Mb/s Ethernet RJ 45 connector ■ 1x RS-232C (D-9 connector) ■ Included software:
Omgevingstemperatuur	5°C up to 40°C
Lamp	2 x 300 Watt UHP lamp Lifetime: 1500 h/lamp
Lenzen	• Fixed lenses: -OGD (0.86:1) R9840491 -OFD (1.27:1) R9840400 -OFD (2.5:1) R9840290 -OFD (7.0:1) R9840410 • Zoom lenses: -OHD (1.4 -2.0:1) R9849930 -OHD (2.1 -3.0:1) R9849810 -OFD (3.4 -4.5:1) R9840060 -OFD (4.5 -6.0:1) R9840100
Lensverschuiving	Vertical: -120% to +120% Horizontal: -50% to +50%
Stoffilters	Dense High Quality Microfilter (front side removeable)
Geluidsniveau	< 39 dB
Netspanning	90V-255V
Energieverbruik	Max. 900 Watt
Vermogensdissipatie	Max. 2900 BTU/hour
Wisselstroom	90V-255V (50 Hz -60Hz)
Gewicht	35 kg (77 lbs)
Afmetingen	D x W x H, without cable basket: 679 x 567 x 282 mm (26.73 x 22.32 x 11.10 inch)
Veiligheidsvoorschriften	Compliant with UL1950 and EN60950
Elektromagnetische storing	Compliant with FCC rules & regulations, part 15 Class A, CE EN55022 Class A and CCC

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.