

SP4K-25B

24,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPureTM**
- **Fit and forget**

SP4K-25 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

Brilliant image

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image ManagementTM includes patented technology to guarantee sharp, consistent image quality over time.

Ready for tomorrow, today

With the SP4K models and their RGB laser lightsource, the Barco ColorgenicTM technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K HFR and IAB audio.

Barco EcoPureTM

This silent running projector (51dB(A)) is fully ready for boothless operation. In addition, the SP4K-25 smartly manages its power consumption reaching projector efficiency levels up to 12 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plateTM spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-25 seamlessly integrates into your current setup.

Product specificaties

SP4K-25B

Algemene specificaties

Oorspronkelijke helderheid	24,000 lumens (typical)
Oorspronkelijke contrastverhouding	2000:1 (typical) up to 3000:1 with HC lens
Digitaal MicroMirror-apparaat™	3x 1.38" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurengamma	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Lichtbron	Laser
Prime-lenzen	0.8; 1.01; 1.13-172; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98 High-brightness and high-contrast B-lenses compatible
Helderheidsstabiliteit op lange termijn	+50,000 hrs @ average usage conditions
Behuizing	integrated cooling design and patented sealed optical assembly
Afmetingen (BxLxH)	Projector incl feet: 760 x 1470 x 612 mm/ 29,92 x 57,54 x 24,09 inches
Gewicht	155kg/342lbs
Stroomvereisten	single phase or triple phase 200-240V 14A
Warmtebelasting (max. vermogen)	7100BTU/h@ max power @ 40°C
Uitlaatluchtstroom	615CFM
Omgevingstemperatuur	40°C/104F Max.
Luchtvochtigheid	85% RH max.
Altitude	4000m / 13.125ft Max.
Mediaserver	Fully Integrated Barco Alchemy ICMP-X with SSD Storage Up To 8TB eff. Other media server brands** supported.
Energieverbruik	2.0kW (3W in Eco mode)
Geluidsniveau	51dB(A) @1m, max power and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Veiligheidseisen	Class 1 risk group 3
Gebruikersinterface	Integrated Touch Display and/or Web-based Communicator Web Analyzer for service

Laatst bijgewerkt: 28 Apr 2025

© 2025 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.