G100 rigging frame

Rigging frame for the G100 series



Rigging frame for the G100 series (*)

(*) When the UST lens (R9802360) is combined with the G100 rigging frame (R9802681), a minimum lens shift is required to avoid shadows. Relative to the center position the lens needs to be shifted upwards by a minimum of 8%, and to the right by a minimum of 21% (100% = half the image height/width). The removable front bar of the frame should also be removed.

It's not recommend to use the G100 rigging frame when building a dual stacked setup using the UST lens



Product specifications

G100 RIGGING FRAME

General specifications	
Size	88.7 x 78.3 x 43.3 cm / 34.9 x 30.8 x 17.1 in
Weight	25.4 kg / 56 lbs

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.

