


Heimdall+

High resolution in a compact format



- **Native 4K Resolution (4,096 x 2,160)**
- **6,000 ANSI Lumens**
- **Solid state RGB Laser**
- **REC.2020 color gamut**

Heimdall is the Norse god who illuminates the world. Our Heimdall guards the Bifrost, having a wide color gamut, capable of displaying vibrant and true-to-life colors, much like the full spectrum of a rainbow.

Heimdall is everything you ever wanted in a home cinema projector ... A stunning native 4K picture with REC2020 color gamut. RGB laser with 6,000 lumens makes large screens shine. HDMI™ 2.1 provides the latest connectivity, perfect for gaming. Multiple lens options provide installation flexibility. And, Barco Residential can't wait to show you additional functionality coming with future firmware updates!

- **RGB Laser light engine** The brand new RGB laser light engine gives Heimdall its incredible brightness with a long lifetime of 25,000 hours, even at full power. The solid state design has no moving parts for the absolute highest reliability.
- **HDMI 2.1 connectivity** Supporting HDMI™ 2.1 and HDCP 2.3 this projector also supports consumer video standards including 4K UHD.
- **Optics** 7 different lenses are available, from ultra short throw to extreme long throw.

- Optics7 different lenses are available, from ultra short throw to extreme long throw. This allows the Heimdall to be installed in virtually any room and in virtually any location.
- Stunning picture qualityHeimdall is Barco Residential's first single chip Native 4K projector for exquisite resolution and detail. The RGB laser light engine provides 98% of the REC2020 color gamut, ensuring faithful reproduction of every color in every movie.
- Next-generation Pulse platformPulse is a hardware and software based platform that simplifies the signal path, allowing it to go from source to screen much faster and more efficiently. We use an advanced image processing technique to display the image on the screen without any artifacts and with virtually no latency at speeds up to 120hz at Native 4K resolution.
- Single Step ProcessingSingle Step Processing (SSP™) provides geometry correction, warping & blending & more for ultimate installation flexibility.

技术规格

HEIMDALL+

一般规格	
投影机类型	4K 1-chip DLP RGB laser projector
光源寿命	25,000 hours: 100% power/25°C/sea-level
安装	Free Rotation
技术	Single Chip 4K DMD, Solid State RGB Laser
分辨率	Native 4K: 4,096 x 2,176 pixels
纵横比	1.88:1
光源	Solid State RGB Laser
光输出	6,000 ANSI lumens
对比度	20,000:1 (with DynaBlack)
输入分辨率	Including and up to: 4,096 x 2,160 @ 120Hz RGB/YCbCr 4:4:4 12bit
镜头系列	Note: All throw ratios adjusted for 0.98" DLP device 0.53:1 (EN67)*
	0.70-1.06:1 (EN66)*
	0.83-1.14:1 (EN76)*
	1.06-1.50:1 (EN63)*
	1.10-1.61:1 (EN83)
	1.48-2.18:1 (EN61)*
	2.19-4.05:1 (EN64)*
	* Requires York lens adaptor (R9802623) for FLDX/FLD+ lenses
光学镜头移位	Varies depending on lens
色彩校正	P7 RealColor™
色域	REC709, DCI-P3, 98% REC2020
图像处理	Embedded warp & blend engine
网络连接	10/100/1000 Mbit
运行湿度	20 -80% RH
HDR	HDR10, HLG
3D	Active Stereoscopic 3D
输入	HDMI 2.1 (HDCP 2.3)
控制	IR, RJ45, Optional Cabled Remote
存储温度	-20 to 60 °C
运输尺寸 (宽 x 长 x 高)	560 x 765 x 410 mm / 22.1 x 30.1 x 16.1 in. (excluding lens)
存储湿度	10 -90% RH
电源要求	7-3A, 100-240V~, 50/60Hz
认证	CE, FCC Class A and cCSAus
功耗	610W typical, 750W maximum
噪音水平 (典型值, 25°C/77°F)	29dB
运行温度	10 -40°C (sea level)
运行湿度	20 -80% RH
每小时 BTU	2,081 BTU/h typical, 2,545 BTU/h maximum
尺寸 (宽 x 长 x 高)	473 x 563 x 293 mm / 18.6 x 22.2 x 11.6 in (excluding lens and feet)
重量	31 kg/68 lbs
保修政策	Limited 3 years parts and labor, extendable up to 5 years
安全要求	RG2 *
	*Only lenses specified in the installation manual are permitted for installation.
	*This projector may become RG3 when no lens is installed.

生成于：30 Apr 2025

© 2025 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。

