

# LC-47

47" native high-definition LCD display



**技术规格****LC-47****一般规格**

技术	TFT LCD
分辨率	1920x1080 (full HD)
寿命	50,000h average
颜色	16.8 million
色阶度	76% NTSC
宽高比	16:9
视角	176°/176°
响应时间	8 ms
颜色调节	3200K, 5400K, 6500K, 9300K, User (R,G,B sliders)
对比度	800:1
亮度	500cd/m <sup>2</sup>
灯传感器	Ambient light sensor for automatic dimming
标准输入	DVI, VGA (D15), S-Video, Composite Video, Component video (YPbPr, YCbCr)
可选输入	External converter HD-SDI/SDI to DVI-D. Inputs: SMPTE-259M-C, SMPTE-292M
支持分辨率	On composite, S-video and component inputs: PAL-Secam 576i, NTSC 480i On DVI and VGA inputs: VESA: VGA, SVGA, XGA, WXGA, SXGA, SXGA+, UXGA; SMPTE-296M(1280 x 720p); SMPTE-274M (1920 x 1080i and 1920 x 1080p)
控制	-RS232 control (with loop-through) -On Screen Display (OSD) -IR remote control
音频	Audio pré-amp input module (excl. speakers)
画中画	PIP source max. 110 MHz
输入	85V-264V (50Hz-60Hz)
功率消耗	303W
工作温度	5° to 40°C (41° to 104°F)
湿度	Max. 85%
校准	CE, UL, FCC, TÜV
冷却方式	Low noise level 21 dB(A) / fanless cooling
屏幕对角线距离	47" (1,194 mm)
可视区域尺寸	1,044 x 590 mm (41.1" x 23.2" )
尺寸	1,139 x 684 x 126 mm (44.84" x 26.93" x 4.96" )
净重	40.2 kg (88 lbs)
吊柜	VESA MIS F, 600, 200, 8 (mounts and table stands are optional)
保修期	Warranty of the Product is two years. Image retention resulting from prolonged continuous use of the Product is not covered by warranty

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。