

RLM H5 Performer

With its compact design and sealed optics, the RLM G5 Performer has proven itself to be an ideal all-round projector suitable to both the rental and staging markets.



Specifiche tecniche**RLM H5 PERFORMER**

Specifiche generali	
Emissione luminosa	4500 ANSI Lumen
Risoluzione	1280 x 720 (native)
Rapporto di contrasto	1000 : 1 (full field)
Modalità contrasto elevato	Available with special lenses
Uniformità della luminosità	> 90%
Lampada	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
Livello di rumore (a 20° C)	42 dBa
Livello di rumore (a 40° C)	46,5 dBa
Temperatura ambiente	Max 40°C (104°F)
Consumo energetico	700 W
Tensione di alimentazione	92-240 V
Peso	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
Dimensioni (PXLXA)	705 x 707,8 x 316,5 mm
Otturatore	Standard
Elemento centrale DLP™ sigillato	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
Commutazione continua	Standard (wipes, fades, ...)
PIP (Picture-In-Picture)	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Zoom digitale	Standard
Encoder obiettivo	On zoom and focus (with TLD lenses)
CLO (Constant Light Output, uscita costante della luce) collegato	not available
Compatibilità sorgente ingresso	1600 x 1200 (max. input)
Ingressi fissi	■ 1x configurable 5 cable (BNC) ■ 1x composite Video (BNC) ■ 1x S-Video (4-pin DIN) ■ 1x analogue RGB (D15 Connector) ■ 1x SDI/HDSDI (+ loop-through) ■ 1x DVI (Digital Visual Interface)
Ingressi modulari	not available
Controllo	· 1 x RS-232 / 422 IN · 1 x RS-232 / 422 OUT · 1 x XLR female (2 way) · build-in RF remote transceiver (optional)

Specifiche tecniche**RLM H5 PERFORMER**

Intervallo spostamento	Lens	Shift Range
	RLD 0.8	up-down: 35<>35 left-right: 15<>15
	Other RLD	up-down: 130<>40 left-right: 50<>50
	TLD (HB) 0.8	up-down: 90<>50 left-right: 40<>40
	Other TLD (HB)	up-down: 140<>50 left-right: 50<>50
Rapporto di proiezione	Lens	Throw ratio
	RLD 0.8	0.64
	RLD 1.5 - 1.8	1.2 - 1.44
	RLD 1.8 - 2.25	1.44 - 1.8
	RLD 2.25 - 3.0	1.8 - 2.4
	RLD 3.0 - 4.5	2.4 - 3.6
	RLD 4.5 - 7.0	3.6 - 5.6
	TLD (HB) 0.8	0.8
	TLD (HB) 1.6 - 2.0	1.6 - 2.0
	TLD (HB) 2.0 - 2.8	2.0 - 2.8
	TLD (HB) 2.8 - 5.0	2.8 - 5.0
	TLD (HB) 5.0 - 8.0	5.0 - 8.0
Informazioni per ordini	R9010300	

Generato il: 15 Mar 2023

Le informazioni e i dati forniti riguardano l'apparecchiatura descritta. Tuttavia ogni singolo articolo è soggetto a modifiche senza preavviso.
L'ultima versione di questo opuscolo è disponibile all'indirizzo www.barco.com.