


LD140-8

Barco's LD LED display solution wraps all the desirable LED qualities of brightness, dependability, long lifetime and low maintenance into an affordable package that meets all your requirements for dynamic digital



Product specificaties

LD140-8

General specifications

Beeldschermgrootte	diagonal: 142" W x H: 3136mm x 1729 mm (124" x 71") surface: 5,6 m² (60 ft²)
Led-type	3-in-1 SMD
Pixelpitch	8 mm
Resolutie	392 x 224
Helderheid	1200 NIT 1000 NIT (display calibrated at 6500° K)
Hor. kijkhoek	145° + (min 50% brightness)
Vert. kijkhoek	145° + (min 50% brightness)
Levensduur	100.000h (typ. use) 45.000h (full white -half brightness)
Verwerking	+12 bit/color
Kleuren	68.7 billion
Vernieuwingssnelheid	400 Hz
Energieverbruik	2.240W (Avg) 8.960W (Max)
Temperatuurbereik	operating: 0° to 40°C (32° to 140°F) storage: -20° to 60°C (-4° to 140°F)
Afmetingen behuizing	width: 3372mm (133") height: 2028mm (80") depth: 330mm (13")
Gewicht	620kg -1367lbs (excl. opt. mounting)
Beeldverwerkingsapparaat	D2

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

