

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.

- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lensrange is designed for the continuing evolution of theDLP technology.

기술 사양

SLM G5 PERFORMER

일반 사양	
광 출력	5,000 ANSI lumens
해상도	1024 x 786 (native) 1600 x 1200 (max)
해상도	1024 x 786 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD's
밝기 균일도	> 90% for the total screen area
명암비	500:1 (full white/full black) 500:1 (full white/full black)
램프	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
소음도(@ 20°C -68°F)	< 43
소음도(@ 40°C -104°F)	< 50
기본 전압	110/230 V
전력 소비	1.600 W
주위 온도	40°C (104°F) max
크기	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
무게(리징 기어 포함)	56 kg / 124 lbs
렌즈	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
렌즈범위	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
실드 DLP™ 코어	Yes
무이음경계선(Seamless) 전환	Standard
ScenergiX	Standard
고정 입력	<ul style="list-style-type: none"> • 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals • 2 Multistandard DVI • SDI input (Serial Digital Input)
옵션형 입력	One free digital input slot for optional input modules: <ul style="list-style-type: none"> • SDI • HD -SDI
원격 제어	<ul style="list-style-type: none"> • RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

작성일: 15 Mar 2023

기술 사양은 예고 없이 변경될 수 있습니다. 최신 정보는 www.barco.com에서 확인하십시오.

ENABLING BRIGHT OUTCOMES

BARCO