


# BARCOVision 8200



**技术规格****BARCOVISION 8200****一般规格**

对比度	5x4 Checkerboard: 120:1 Full Field Contrast: 300:1
深度	1162 mm / 46 inch
高度	366 mm / 14 inch
输入	Communication: 1 D9-female Stereo Audio: 2 x Cinch (RCA) RGB trilevel sync, sync on green or sync separate: 5 x BNC (Optional) RGB analog standard sync, sync on green or sync separate or composite sync: 5 x BNC (Optional) Component Video: 4 x BNC (Optional) Video/S-Video: 1 x BNC/4-pin DIN (Optional) RS232 loop-through: 1 x D9-female
光输出	2500 ANSI Lumen
输出	RS232 loop-through: 1 x D9-male
分辨率	Maximum Resolution through windowing: 800 x 600
屏幕尺寸	Minimum Screen Width 1m Maximum Screen Width 5m
净重	Net weight: 70 kg / 154 lbs Shipping weight: 110 kg / 243 lbs
宽度	630 mm / 25 inch

**生成于: 09 Jul 2024**

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。