

# WSG-110

Small form factor thin client for SecureStream



**Barco's WSG-110 thin client is a small form factor to display encoded streams coming from an IP network. It supports standard H.264, Barco's low-latency Video2Data (V2D), Barco ProServer/Virtual Network Computing (VNC) and Remote Display Protocol (RDP) decoding.**

## **Low noise thin client for up to two displays**

The WSG-110 is designed and fully qualified for Barco's SecureStream solution. Once connected to a SecureStream system, the pre-configured appliance enables customers to capture networked source information from anywhere. It displays these sources with a user-friendly user interface.

Multiple appliances can be combined to show sources as part of a composed desktop on monitors of an OpSpace workstation, a truly unified workspace for mission-critical applications.

This thin client can process up to eight HD-quality sources and allows organizing visual and interactive content as a smart multi-viewer to enhance knowledge and improve decision-making.

## **Features**

- Pre-configured thin client for SecureStream
- Linux based operating system
- Intel ® i7 Quad Core TM processor for low-latency application processing and software based media decoding

- Processes up to eight HD sources
- Universal IP streaming video decoding (H.264, V2D, ProServer/VNC, RDP)
- Silent operation
- Small form factor
- Flexible mounting options

| Технические характеристики |                                                                                                                  | WSG-110                                   |
|----------------------------|------------------------------------------------------------------------------------------------------------------|-------------------------------------------|
| Общие характеристики       |                                                                                                                  |                                           |
| Платформы                  | SecureStream                                                                                                     |                                           |
| Процессор                  | Intel(R) Core(TM) i7 Quad core CPU 3.4GHz                                                                        |                                           |
| Память                     | 8 GB RAM                                                                                                         |                                           |
| Жесткий диск               | 128 GB SSD                                                                                                       |                                           |
| Сеть                       | 2x 1Gb/s LAN                                                                                                     |                                           |
| Графический адаптер        | Intel HD Graphics 630                                                                                            |                                           |
| Выходы                     | Up to 2x displays HD 1920x1200 @60Hz via DisplayPort (HDMI via included adapters)                                |                                           |
| Ввод                       | IP video sources (H.264), Video2Data (Barco V2D), Virtual Network Computing (VNC), Remote Desktop Protocol (RDP) |                                           |
| Фактор формы               | 60 x 190 x 190 mm   2.36 x 7.48 x 7.48 in<br>Packed: 230 x 260 x 308 mm   9.06 x 10.24 x 12.13 in                |                                           |
| Вес                        | 2.2kg<br>Packed: 4.5kg                                                                                           |                                           |
| Электропитание             | External PSU 150W / 90 – 264 VAC / 47 – 63 Hz                                                                    |                                           |
| Энергопотребление          | Typ. 83W   max. 110W                                                                                             |                                           |
| Диапазон температуры       | 0° -40° C   32° -104° F                                                                                          |                                           |
| Влажность                  | Max. 80% (non-condensing)                                                                                        |                                           |
| Наработка на отказ         | 47,500 h                                                                                                         |                                           |
| Уровень шума               | Max. 32dbA (measured at 1m/32.8ft distance at 22°C/72°F)                                                         |                                           |
| Соответствие               | CE, CB, UL, RCM, BIS, CU-EAC, FCC Class A<br>CCC contact Barco Sales                                             |                                           |
| Монтаж                     | Order no.                                                                                                        |                                           |
|                            | R9811098                                                                                                         | P110 VESA Mount (for 1x OPS-110 + 1x PSU) |
|                            | R9811099                                                                                                         | P110 Rack Mount (for 2x OPS-110 + 2x PSU) |

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте [www.barco.com](http://www.barco.com) для получения последних спецификаций.

[www.barco.com](http://www.barco.com)

