

# MXRT-6700

8GB high-performance display controller



- **Optimal performance**
- **Reliable longevity**
- **Guaranteed workflow support**

## Ultimate solution for mainstream diagnostic imaging

The high-performing Barco MXRT-6700 graphics card is a versatile solution with the power and features necessary to meet most diagnostic imaging needs. With 8GB of graphics memory driving four DisplayPort v1.4 outputs, it is the ideal solution for organizations looking to standardize on one controller across their entire fleet of reading stations.

Accelerate your workflow application responsiveness with 1792 stream processors and enable more efficient data transfers between the GPU and CPU with PCIe® 3.0 support. Key features include 4 ports to cover expanded display arrays, increased memory for larger image data loading, EDID emulation for multi-workstation configurations, and Thunderbolt™ 3 compatibility for eGFX applications.

- 8GB GDDR5 display memory
- 160 GB/s memory bandwidth
- 256-bit memory interface
- 4 DisplayPorts 1.4
- Maximum power consumption: 75W

## Product specifications

## MXRT-6700

### General specifications

|                           |   |
|---------------------------|---|
| Bus compatibility         | PCIe Gen3 x16   |
| Power consumption         | 75 W  |
| Form factor               | 173mm (L) x 112mm (H) single wide PCIe slot   |
| Operating system          | Windows 11 (64-bit), Windows 10 (64-bit)  |
| Platforms                 | Intel® and AMD architectures  |
| Power Connector           | None  |
| Graphics accelerator      | AMD Radeon Pro™   |
| Display memory            | 8GB DDR5  |
| Memory interface          | 256-bit   |
| Memory bandwidth          | 160 GB/s  |
| Pixel depth               | 32-bit pixels (10-bit grayscale and 30-bit color)   |
| Electrical standard       | DisplayPort (DP) v1.4   |
| Direct3D hardware support | Microsoft® DirectX v12, Vulkan® 1.1, Shader Model 5.1   |
| OpenGL hardware support   | OpenGL 4.5  |
| Connectors                | (4x) DisplayPort 1.4  |
| Approvals and compliance  | FCC Part 15 Class B, CE EN 55032 Limit B, EN 55024, UL-60950-1, BMSI CNS, CISPR-32/24, IEC609050-1, VCCI, CSA C22.2, EU RoHS directive (2011/65/EU), Certificate of Information & Communication Equipment (Republic of Korea) |
| Connectivity              | Native DisplayPort suggested<br>DisplayPort to Single-link DVI adapter available separately   |
| Operational temperature   | 0° to 55°C  |

Last updated: 05 Mar 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.