

PJWU-101B

11,000 ANSI lumens, WUXGA, single-chip DLP projector



10K
LUMENS

1
CHIP
DLP

- **The brightest 1-chip DLP projector**
- **Excellent image quality**
- **Designed for large-screen projection**

This product is only available in China and via distribution partners.

With its 11,000 ANSI lumens brightness and WUXGA resolution, this projector is the brightest single-chip DLP projector currently available.

What you'll love about this projector

- Stylish design that seamlessly blends in with your office interior
- High-quality images with an unmatched level of detail and contrast
- Button-free and cable-free for simple operation and less clutter
- Reliable DLP technology for true ease of mind
- Easily upgradable with future connectivity add-ons
- Low cost of ownership thanks to DLP technology and sealed optics
- Preset image modes that allow for flexible color management
- Intuitive control menu with the most common features at your fingertips
- User-friendly remote control that features just one button

Product specificaties**PJWU-101B****General specifications**

Type projector	WUXGA single-chip DLP projector
Technologie	0.96" DMD
Kleurencirkel	65 standard (RGBYCW)
Resolutie	1,920 x 1,200 WUXGA
Helderheid	11,000 ANSI lumens / 7,500 ANSI lumens (eco mode)(compliant with ISO 21118)
Contrastverhouding	1,500:1
Helderheidsuniformiteit	85%
Beeldverhouding	16:10
Type lens	J lens
Lenzen	2.4 -4.0:1; 1.85-2.4:1; 1.56-1.85:1; 0.84-1.03:1
Optische lensverschuiving	Vertical: +/-100%; horizontal: +/-30% / Vertical: +/-75%; horizontal: +/-25% (for 0.84-1.03:1 lens)
Kleurcorrectie	Yes
Lampen	2 x 465W Ushio
Levensduur lamp	Up to 1,500 hours (full power), up to 2,500 hours (eco mode)
Transport met lamp	Yes
Verzegelde DLP™-kern	Yes
Optische dowser	Yes
Geavanceerde Picture-in-Picture	Yes
Oriëntatie	table -ceiling
Geïntegreerde webserver	Yes
Trapeziumcorrectie	Yes
Ingangen	5 BNC, VGA, HDMI-1, HDMI-2
Invoerresoluties	up to WUXGA (1,920 x 1,200) 60Hz
Softwaretools	Projector Toolset
Controle	IR, RS232, RJ45
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	100-240V / 50-60Hz
Max. energieverbruik	1,180W @110 VAC/1,100W @ 220VAC; 890W @110 VAC/860W @ 220 VAC (eco mode); less than 2W (standby)
Geluidsniveau (standaard bij 25°C/77°F)	45 dBA (typical in bright mode) / 40 dBA (typical in eco mode)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	30-90%
Afmetingen (B x L x H)	670 x 530 x 285 mm
Gewicht	33 kg
Verzendingsafmetingen (L x B x H)	829 x 709 x 437 mm
Verzendgewicht af fabriek	42 kg
Certificeringen	CB test certificate, US emc, US safety, CE emc and safety, CCC emc and safetyh
Garantie	3 years standard warranty (warranty and service conditions can differ from region to region. Contact your local sales or service rep for more details)

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO