

BARCOData 708 + Iris³



技術仕様

BARCODATA 708 + IRIS³

一般仕様	
互換性	Horizontal autolock scan frequency of 15-69 kHz Vertical autolock scan frequency of 37-210 Hz Standard Video, S-Video and professional Component Video RGB signals from a wide range of PC graphics boards with resolutions up to 1280 by 1024 pixels/60 Hz Wideband 75 MHz RGB amplifiers A full complement of input signal connections
コントラスト	>1000:1 (full field contrast)
光出力	1100 Lumen (at 10 % peak white) 130 ANSI Lumen (Economy mode) 170 ANSI Lumen (Normal mode) 200 ANSI Lumen (Boost mode)
対応スクリーンサイズ	Min.: 1.4 m x 1.05 m (4.6' x 3.5') Max.: 6 m x 4.5 m (20' x 15')

生成日:09 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

