

RetroGraphics 808s



- Single front surface-coated optical grade mirror
- 67" super fine pitch Fresnel/Lenticular-Blackstripe screen with very wide horizontal and vertical viewing angles
- High-definition 8" CRTs with electromagnetic focus system
- F1.1 color corrected hybrid liquid coupled lenses
- Optional built-in Video Line Doubler improves Video image quality
- Horizontal autolock scan frequency of 15-110 kHz
- RGB bandwidth of 120 MHz
- Vertical scan frequency of 37-200 Hz
- Displays all sources from VHS Video up to 1,600 x 1,200 pixel workstations

技術仕様

RETROGRAPHICS 808S

一般仕様	
互換性	Display compatibility of from VHS Video up to 1600 by 1200 pixel workstations Horizontal autolock scan frequency of 15-110 kHz Vertical scan frequency of 37-200 Hz RGB bandwidth of 120 MHz Universal connection possibilities
コントラスト	>1000:1 (on full white / full black)
光出力	1250 Nit / 364 ftL. (at 10 % peak white) 139 Nit / 41 ftL ANSI (Economy mode) 195 Nit / 57 ftL ANSI (Normal mode) 214 Nit / 62 ftL ANSI (Boost mode)
対応スクリーンサイズ	(diagonal) 67" (1.7 m)

生成日:08 Jul 2024

© 2024 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。

