


# Input Controller 16

Input Controller 16



- 16 fully configurable inputs One output 19 inch rack mount Standard equipped with Xlite Toolset, controlling software. Multipurpose device: both Daylight Display and Projection Arrange your sources onto your display through an intuitive interface. Scale and position all sources exactly how you want them. Overlay sources using advanced chroma-keying and alpha blending features. Process video and data in pure quality onto your display. Compatible with all standard image formats.

## Spécifications techniques

## INPUT CONTROLLER 16

### Spécifications générales

Entrée	16 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
Compatibilité	Barco Daylight Displays Projectors
Sortie	DVI-A, DVI-D, RGB
Contrôle	· Scaler  16 input channels [Data-Video] fully scalable to desired output resolution · Z-order  Instant modification of Z-order control, for each output window · Window positioning  Intuitive positioning interface · Connectors  RS 232 [RJ11]
Effets	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
Température de fonctionnement	0° <-> 45°
Alimentation	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
Référence	R9851580

Créé le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter [www.barco.com](http://www.barco.com) pour les dernières spécifications.