

# SP4K-20

20,000 lumens smart cinema projector



20K  
LUMENS

4K  
4096X2160



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure<sup>TM</sup>**
- **Fit and forget**

SP4K-20 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

### Brilliant image

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management<sup>TM</sup> includes patented technology to guarantee sharp, consistent image quality over time.

### Ready for tomorrow, today

With the SP4K models and their RGB laser light source, the Barco Colorgenic<sup>TM</sup> technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

### Barco EcoPure<sup>TM</sup>

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-20 smartly manages its power consumption reaching projector efficiency levels up to 9.5 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate<sup>TM</sup> spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-20 seamlessly integrates into your current setup.

**Product specificaties****SP4K-20****General specifications**

Native helderheid	20,000 lumens (typical)
Native contrastverhouding	2300:1 (typical)  up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 0.98" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurenspectrum	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Lichtbron	Laser
Primelenzen	With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9  With B-lensholder: 1.01; 1.27; 1.6 – 2.4; 1.9 – 2.6; 2.0 – 2.95; 2.3 – 3.65; 2.8 – 4.7; 3.55 – 6.95  High-brightness and High-contrast B-lenses compatible
Langdurige stabiliteit van helderheid	40,000 hrs @ average usage conditions
Behuizing	integrated cooling design and patented sealed optical assembly
Afmetingen (B x L x H)	Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches 710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder
Gewicht	105kg/231.5lbs
Voedingsvereisten	single phase or triple phase 200-240V 16A
Warmtebelasting (max. vermogen)	6800BTU/h
Luchtuitstroom	400CFM
Omgevingstemperatuur	40°C/104F Max.
Omgevingsvochtigheid	85% RH max
Mediaserver	Barco Alchemy ICMP-X and other media server brands** supported.
Energieverbruik	2.1kW (3W in Eco mode)
Geluidsniveau	50dB(A) @1m and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Veiligheidsvereisten	Class 1 risk group 3
Gebruikersinterface	Touch Display and / or web-based
Laterale lenskleur op beeldrand	With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...)
Opmerkingen	**projector configuration with ICP-D; contact Barco service for the list of supported brands

**Laatst bijgewerkt: 09 Jul 2024**

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.