

FLDX lens 0.38 : 1 UST 90°



Product specifications**FLDX LENS 0.38 : 1 UST 90°**

General specifications	
Lens type	FLDX 0.38 : 1 UST 90°
Working F/#	2.4
Zoom ratio	1
Platforms	F35, FL40, F70, F80*, F90 and G100** *For use with F80: Lens requires lens adapter (R98014421) **For use with G100: Lens needs lens adapter (R9802360) and lens support system (R9802365)
Throw Ratio	DMD chip WUXGA (F35, FL40, F70, F90 and G100): 0.38 : 1 WQXGA (F35, FL40, F70 and F90): 0.41 : 1 WQXGA+ (F80): 0.54 : 1 Image size tolerances +/-2%
Focal length	8.2mm
Focus Range	Standard 133" – 400" for F80, 200" – 600" for F35, FL40, F70, F90 and G100
Throw distance	1.6 -5 m
Motorized Zoom	N/A
Motorized Focus	Yes
Weight	Net: 6.6 kg Gross: 9.7 kg

Last updated: 03 Nov 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.