

BarcoMed 5MP2FH PCI

Ultra-fast PCI display controller for digital mammography



Product specifications**BARCOMED 5MP2FH PCI****General specifications**

Bus	PCI 2.2 universal signaling
Power consumption	< 15 Watt
Form factor	167.6 x 106.7 x 15 mm (6.6 x 4.2 x 0.6")
Operating system	Win XP 32/64, Server 2003, 2008, Vista XPDM
Display configuration	Dual-head portrait or landscape
Graphics processor	AURA technology
Display memory	512MB
Pixel clock rate	340 MHz
Electrical standard	Dual DVI complying to VESA A DVI Rev. 1.0 spec
Supported resolutions / refresh rates	<ul style="list-style-type: none">■ 2048 x 2560 @ 50Hz■ 2096 x 2800 @ 50Hz
Operational temperature	0° to +60°C (32° to 140°F)
EMI	<ul style="list-style-type: none">■ FCC class B■ CISPR22 Class B■ BSMI CNS■ VCCI■ EN55022■ EN55024■ EN60950■ CE■ UL60950-1■ CSA C22.2

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.