


OLite 510

Multifunctional indoor/outdoor SMD LED tile (5000 nits, 10mm pixel pitch) that can be broken down into 64 discrete modules to create LED displays of any shape or form.



Product specificaties

OLITE 510

General specifications	
Pixelpitch	10 mm
Gekalibreerde helderheid	5000 NIT
Led-configuratie	3-in-1 SMD
Pixeldichtheid	5.632 LEDs per tile (88 x 64 px)
Hor. kijkhoek	> 145°
Vert. kijkhoek	> 95°
Contrast	810
Levensduur	50.000 hours
Energieverbruik	970 W/tile (max) 275 W/tile (average)
Gewicht / tegel	58 kg (127.9 lbs)
Verwerking	15,8 bit per color at 50Hz
Kleuren	185 trillion
Vernieuwingssnelheid	800 Hz minimum (PAL/NTSC)
Bereik bedrijfstemperatuur	-20 to 45°C (-4 to 113°F)
Opslagtemperatuur	-20 to 60°C (-4 to 140°F)
Operationele vochtigheid	10 -99%
Vochtigheid bij opslag	10 -99%
Opbouw truss	Max. 15 tiles high
Opbouw voet	Max. 12 tiles high
D320-invoercompatibiliteit	S-Video, Composite, YUV, RGB, SDI, HDSDI, Data: DVI up to UXGA
Certificeringen	UL, CE, FCC Class A, TUV

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

