

D-Cine Premiere DP100

2k Digital Cinema projector for large screens up to 20m (65.6ft)



Specifiche tecniche

D-CINE PREMIERE DP100

Specifiche generali

Emissione luminosa	22,000 cinema lumens
Digital MicroMirror Device™	3 x 1.2" dark metal type Advanced DLP Cinema™ signal processing: CineCanvas™ image management; CinePalette™ color management, CineBlack™ contrast management and CineLink™ security management
Risoluzione nativa	2048 x 1080
Alloggiamento	Hermetically sealed DMD™ and optical assembly
Larghezza schermo	Screen width (screen gain 1.8) @ 14ftL: 25m -82ft adjustable light output CLO software
Montaggio	Standing on pedestal, including caster & wheels Up to 15 degrees tilt on pedestal
Lampada	1.5k to 7k Xenon arc lamp sizes Compatible with standard and high performance lamp types
Rapporto di contrasto	2000:1
Ingressi video digitale	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Obiettivi a focale fissa	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Diagnostica del proiettore	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
Requisiti di alimentazione	3 x 400V + N or 3 x 220V version available max. 29,250 BTU/hr (with 6.5kW lamp)
Dimensioni:	projector head: 640(H) x 730(W) x 1186(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch projector head + pedestal: 1466(H) x 730(W) x 1252(D) mm / 57.7(H) x 28.7(W) x 49.3(D) inch
Peso	projector head + pedestal: approx. 205kg (452lb)
Opzioni	- CLO -Constant Light Output control - Anamorphic lens fitting for 1.25:1 scope lens - Acsar 2 Alternative Content Input Processor - ImagePRO HD - SNMP agent (v3)
Informazioni per ordini	EU: R9010111 US: R9010118

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.