


D-Cine Premiere Console Kinoton EUR



Product specifications**D-CINE PREMIERE CONSOLE KINOTON EUR****General specifications**

General	Kinoton, SK25DC console.
Lamp	Optional 2kW, 3kW, 5kW, and 7kW Xenon Arc lamp depending on screen size.
Reflector	Standard f2.0 dichroic glass type
Power supply	-Lamp power supply -EUR version -IREM 3-7 kW three phase 360-460V 50 Hz -Lamp Power supply -USA version -IREM 3-7kW three phase 187-230V 60 Hz

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.