

BlendPRO-II

BlendPRO-II adds widescreen blending capability to the ScreenPRO-II family.



Product specifications**BLENDPRO-II****General specifications**

Video Input	Input Types: Four (4) Digital DVI channels per DDWG 1.0 on DVI-I connector Resolution: VGA up to UXGA @60 Hz (including all progressive HD resolutions and 1920x1200 and 2048x1080)
Video Output	Four (4) high resolution channels Digital DVI channels per DDWG 1.0 on DVI-I connectors and Analog RGBHV on HD-15 connectors
User Control	Controlled from ScreenPRO-II controller via Ethernet
Physical	2 RU Rackmount Chassis
Input power	100-240 VAC, 50-60 Hz, 175 W max.
Environmental	Temperature: 0-40 degrees C; Humidity: 0-95% non-condensing

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.