

CVHD-31B

3,000 lumens, Full HD, single-chip DLP projector



- **Razor-sharp images with vibrant colors**
- **Large lens shift range for flexible installation**
- **Compact design**
- **24/7 reliability**

*Only available at selected distributors

The CVHD-31B will perfectly complement your meeting room, conference room or boardroom.

A compact projector

Combining a brightness level of 3,000 lumens with Full HD resolution, the CVHD-31B is a compact projector. Weighing only 2.9 kg, it is lighter than comparable projectors and in size it's more than 25% smaller!

Crisp and vivid images

The CVHD-31B provides razor-sharp, stable and high-contrast images that allows meeting participants to concentrate better and focus longer. It always shows vivid colors, in excellent quality.

Small footprint, ultimate performance

The CVHD-31B features a filter-free design and reliable DLP technology for unmatched picture accuracy and low total cost ownership. Designed for unlimited use, it also comes with a three-year warranty, for true peace of mind.

Product specifications**CVHD-31B****General specifications**

Technology	optical lens shift design
Resolution	1,920 x 1,080 (Full HD)
Brightness	3,000 ANSI lumens
Projector type	Single-chip DLP projector
Contrast ratio	2,500 : 1
Brightness uniformity	>80%
Aspect ratio	16:9
Lens type	All glass lenses
Lenses	Standard Zoom lens (1.64-2.06:1)
Optical lens shift	Vertical
Color correction	RealColor™
Lamps	220W UHP lamp
Lamp lifetime	Up to 2,250 hours (full power) / 3,000 hours (eco mode)
Lamp house, quick replace	Yes
Lamp warranty	500 hours or 90 days
Sealed DLP™ core	Yes
Orientation	Table – ceiling (360 degrees through portrait mode)
3D	No
Inputs	1 x HDMI (1.3), 1 x DVI-D, 1 x VGA, 1x RCA composite video, 1 x 4-pin mini DIN Y/C, 1 x RCS x3 YUV
Input resolutions	1,920 x 1,200 -640 x 480 pixel resolution (model dependent) / RGBHV, RGBS, RGsB
Software tools	Projector Toolset
Control	IR, RS232, Ethernet
Network connection	1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 1 x USB
Power requirements	3.0-1.3A, ~100-240V, 50-60Hz
Power consumption	Max 290W
Noise Level	30 dB
Operational ambient temperature	10 -40 °C (storage temperature: -20 -60 °C)
Operating humidity	20 -80% RH
Dissipation BTU	Less than 1,061/hour
Dimensions (WxLxH)	278 x 234 x 94 mm / 10.94 x 9.21 x 3.70 inches
Weight	2.9 kg (6.39 lbs)
Standard accessories	Power cord, wireless remote control
Certifications	CE, FCC Class A and cCSAus
Warranty	Limited 3 years parts and labor. Extendable up to 5.

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.