

S70

Stand-alone 70" display for monitoring,
control or collaboration with SXGA resolution and multiple input capabilities.



技术规格

S70

一般规格

| | |
|---------|--|
| 电源 | 95-230 VAC ± 10%, 50-60 Hz |
| 亮度均匀性 | > 95% |
| 通信 | <ul style="list-style-type: none">· 2 x D9 connectors for RS232 in/out· 1 x D9 connector for Com 800· 1 x Mouse Out (DIN 13)· 1 x Mini-jack for wired RC· 1 x IR receivers |
| 兼容性 | <ul style="list-style-type: none">· All current video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, S-VHS, RGB or component forms· All currently proposed HDTV, extended and improved television standards (Eureka 95, Hi-vision, ACTV, IDTV, EDTV ...)· All computer graphics formats from VGA, SVGA, XGA to SXGA· Most Macintosh computers· Electronic workstations with a resolution up to 2,000x1,280 pixels at 76 Hz· Most sources with a pixel clock up to 200 MHz |
| 对比度 | 350:1 |
| 深度 | The unit is 797 mm deep and has a footprint of 603 mm |
| 运行环境 | Ambient temperature 0-40°C 30-105°F at max. 80% humidity (non condensing) |
| 高度 | 1952 mm |
| 高度, 含轮子 | 2003 mm |
| 输入 | <ul style="list-style-type: none">· 1 x 5 BNC for: RGB, component video, composite video, S-video· 1 x S-video (4-pin mini-DIN)· 1 x Video (BNC or cinch)· 1 x VGA (D15) connector· 3 x Stereo audio L/R (cinch) Optional: <ul style="list-style-type: none">· 1 x Serial Digital Input/Output SDI/SDO· 1 x IEEE1394 FireWire |
| 灯泡 | 100 Watts perfectly pre-aligned UHP™ lamp with an operation time of 8000 hours |
| 液晶面板 | 3 active matrix Poly-Silicon LCD panels (1.8" diagonal), with a resolution of 1,280x1,024 at 24 bit/pixel for 16.7 million colors |
| 光输出 | Brightness: 110 cd/m ² or 500 lumens |
| 输出 | <ul style="list-style-type: none">· 1 x VGA (D15) connector· 1 x Stereo audio L/R (cinch)· 1 x Trigger Output Mini-jack |
| 功率消耗 | Typ. 220 Watts |
| 远程控制 | All controls are accessible through a soft-touch panel or a new user-friendly backlit IR remote control: <ul style="list-style-type: none">· Source switching· User settings per source· Installation/Service adjustments |
| 扫描频率 | Horizontal: 15 kHz-115 kHz Vertical: 25 Hz-150 Hz |
| 屏幕尺寸 | The screen has an all around visibility. It is the Fresnel lens that provides the evenness of image brightness. Two or more S70 displays can be lined up side by side with a seam of less than 2 mm. |
| 屏幕宽度 | 1360 mm x 1088 mm 53.5 in. x 42.8 in. |
| 特殊性能 | <ul style="list-style-type: none">· Cabling, operation and servicing (front access)· Available on wheels or with adjustable feet· In case of adjustable feet, height of support on customer' s request· Built-in 2x3 Watt stereo audio amplifier· Color temperature adjustment (broadcast 3200°K, film 5400°K, video 6500°K, computer 9500°K or custom)· Fits through regular doors· Autostart function |
| 净重 | total weight 149 kg 348.33 lbs |
| 宽度 | 1552 mm |

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。