


# TF-20 half-sized

Outdoor 20mm LED tile for fixed installation



## 技术规格

## TF-20 HALF-SIZED

### 一般规格

像素间距	20 mm
校准亮度	7,200 nits
LED配置	1R, 1G, 1B
像素密度	1,152 pixels/panel (48x24)
水平观察角度	120° (min 50% brightness)
垂直视角	+45° (from below) -15° (from above) (min 50% brightness)
对比度	4,000:1
功率消耗	maximum: 400W/m <sup>2</sup> average: 120W/m <sup>2</sup>
重量 / 层数	38 kg (84 lbs)
处理	16-bit/color
颜色	281 trillion
刷新率	800 Hz
崎岖不平	front: IP65 back: IP 54
温度范围	operating: -35°C to 50°C (-31°F to 122°F) storage: -35 to 50°C (-31°F to 122°F)
湿度	operating: 10% to 99% storage: 10% to 99%
认证	UL/ETL, CE, FCC Class A, RoHS, CCC, CETL
瓦状尺寸	960mm x 480mm x 268mm
可维护性	Front/back access, to be specified at order
商品编号	front: R9004814 back: R9004815

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。