

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.
- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Технические характеристики

SLM G5 PERFORMER

Общие характеристики	
Светоотдача	5.000 ANSI lumens
Разрешение	1024 x 786 (native) 1600 x 1200 (max)
Разрешение	1024 x 786 (native) 1600 x 1200 (max)
Цифровое микрозеркальное устройство Digital MicroMirror Device™	3 high resolution XGA DMD's
Однородность яркости	> 90% for the total screen area
Контрастность	500:1 (full white/full black) 500:1 (full white/full black)
Лампа	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Уровень шума (@ 20°C -68°F)	< 43
Уровень шума (при 40°C -104°F)	< 50
Напряжение электрической сети	110/230 V
Энергопотребление	1.600 W
Окружающая Температура	40°C (104F) max
Размер	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Вес (включая монтажный механизм)	56 kg / 124 lbs
Объективы	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Перемещение объектива	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Ядро Sealed DLP™	Yes
Удобная коммутация	Standard
ScenergiX	Standard
Фиксированные входы	• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals • 2 Multistandard DVI • SDI input (Serial Digital Input)
Факультативные входы	One free digital input slot for optional input modules: • SDI • HD -SDI
Дистанционное управление	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

Создано: 15 Mar 2023

Технические характеристики могут изменяться без предварительного уведомления. Для получения самой последней информации посетите веб-сайт www.barco.com.