

SLM R9+ Performer

Compact, SXGA+ resolution and 9000 Ansi Lumen light-output.



Product specificaties**SLM R9+ PERFORMER****General specifications**

Lichtuitvoer	9000 ANSI Lumens 9500 Center Lumens	
Resolutie	1400 x 1050 (native)	
Helderheidsuniformiteit	> 90% for the total screen	
Contrastverhouding	1600 : 1 (full field) High contrast mode: 2000 : 1	
Beeldscherm	3 Chip DLP SXGA+ (resolution of 1400 x 1050 pixels (aspect ratio 4:3)).	
Kenmerken	■ Picture in picture ■ Seamless switching with effects ■ Standard light shutter ■ Rigging point ■ Carrying handle ■ High contrast mode ■ P7 color processin	
Picture-in-Picture	2 sources simultaneous	
Ingangen	Fixed inputs ■ 2x Configurable 5-Wire (BNC; incl. 2 video decoders) ■ 2x DVI (Digital Visual Interface) Modular inputs Standard: ■ 1x SDI (+ loop through) Optional: ■ 1x HDSDI (+ loop through)	
Uitgangen	DVI out (1400 x 1050) of full screen composed image	
Communicatie	■ 1x RS-232C IN (D-9 connector) ■ 1x RS-232C OUT (D-9 connector) ■ 1x RS-232C IN (XLR connector) ■ 1x 2way prop. protocol to Rugged remote (5 pins XLR connector) ■ 1x prop. protocol (RJ45 connector) ■ mini-jack for wired remote control	
Compatibiliteit	· All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats · All currently proposed HDTV, extended and improved television standards (1080i, 720p) · All computer graphics formats from VGA, SVGA, XGA, SXGA, full HD to UXGA · Most Macintosh computers · Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz · Most computer sources with a pixel clock up to 200 MHz · DVI sources up to SXGA+	
Compatibiliteit invoerbron	max. input: up to 1920 x 1080 and 1600 x 1200	
Schermaformaat	From 1-8m / 3-26ft recommended	
Scanfrequenties	Pixel clock >162Mhz (UXGA 60hz)	
Netwerkverbinding	Optional (10 base-T)	
Geïntegreerde beeldschermserver	Optional DIMM PC available Remote control projector over ethernet via webserver	
Omgevingstemperatuur	Max 35°C (95°F)	
Lamp	1.75 kW Xenon	
Lenzen	Warranty univeral lamphouse: 1000 Hrs	
	Lens	Order nr
	TLD (HB) 0.8	R9842040
	TLD (HB) 1.2	R9840770
	TLD (HB) 1.6 - 2.0	R9842060
	TLD (HB) 2.0 - 2.8	R9842080
	TLD (HB) 2.8 - 5.0	R9842100
Lensverschuiving	TLD (HB) 5.0 - 8.0	
	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)	
Lens-encoders	On zoom and focus (with TLD lenses)	

Product specificaties

SLM R9+ PERFORMER

Projectieverhouding	Lens	Throw ratio
	TLD (HB) 0.8	0.75
	TLD (HB) 1.2	1.1
	TLD (HB) 1.6 - 2.0	1.45 - 1.85
	TLD (HB) 2.0 - 2.8	1.85 - 2.55
	TLD (HB) 2.8 - 5.0	2.55 - 4.55
	TLD (HB) 5.0 - 8.0	4.55 - 7.3
	TLD+ (HB) 7.5 - 11.2	7.5 - 11.2
ScenergiX	Standard horizontal and vertical electronic edge blending	
Verzegelde DLP™-kern	Standard	
Stoffilters	Dense, high quality microfilters available as spare kit, in a 6-pack & 24-pack	
Geluidsniveau	61 dBA (at 40°C)	
Netspanning	200-240 V	
Energieverbruik	2250 W	
Vermogensdissipatie	Max 6830 BTU/h	
Wisselstroom	190V -255V (50Hz -60Hz)	
Gewicht	56 kg (124 lbs)	
Afmetingen	WxLxH 585 x 876 x 429 mm (23.0 x 34.5 x 19.9 inch)	
Veiligheidsvoorschriften	Compliant with UL1950 and EN60950	
Elektromagnetische storing	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A	
Bestelgegevens	Projector: R9010320	
	Spare lamp: R9841810	
	6-pack dust filters: R8454096K	
	24-pack dust filters: R84540924K	

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

