

PresentationPRO-II

PresentationPRO-II simplifies presentations, live events, corporate boardrooms, and church services.



Product specifications

PRESENTATIONPRO-II

General specifications

Scaled Video Channel Inputs

Input Types

- Analog Inputs (8) - RGBHV/RGBS/RGsB computer video, YPbPr video (SD or HD), S-video, or Composite video on 15-pin HD connector
- SDI Input (1) – per SMPTE 259M-C on BNC connector (PresentationPRO-II Digital Only)

Input resolutions

- PAL or NTSC
- Computer Resolutions VGA (640 x 480) through UXGA (1600 x 1200)
- HDTV Resolutions up to 1920 x 1080 (720p, 1080i, 1080p)
- Plasma Display Resolutions

Unscaled Background /Key Channel Input (Optional)

Input Types

DVI Digital Input -per DDWG 1.0 on DVI-I connector

Input resolutions

Resolution must be same as selected output resolution.

Outputs

Output Types

- Analog Output - RGBHV/RGBS/RGsB (non-interlaced only) on 15-pin HD connectors
- DVI Digital Output - per DDWG 1.0 on DVI-I connector

Output Resolutions

- Computer Resolutions VGA (640 x 480) through UXGA (1600 x 1200)
- HDTV Resolutions, progressive up to 1920 x 1080(1080p)
- Plasma Display Resolutions

User Control

Front Panel Control

LCD TouchScreen Display, Keyboard circuitry, Rotary Encoders and LED lighted push buttons

Remote control

The unit may be controlled from a computer or external controller via LAN or an RS-232 serial link. Control functions include:

- Source Input Configuration
- Output Format Selection
- Test Pattern Selection
- Video Source Selection
- Transition Effect Selection

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.