

iQ R400



Spécifications techniques

IQ R400

Spécifications générales

Luminosité	4000 ANSI lumens
Uniformité de la luminosité	>95 % for the total screen
Panneaux LCD	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Résolution	1366 x 1024 (native)
Mise en réseau	iQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor - Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory up to 64 MB -Inputs and outputs ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45 connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Lampe	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Lentilles disponibles	· Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (Long throw). · Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.
Largeur d'écran recommandée	From 1-6 m/3-20 ft.
Taux de contraste	>400 : 1 (full white/full black)
Fréquences de balayage	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Caractéristiques	· Standard cable basket · Standard light shutter · Advanced digital zoom · Advanced picture-in-picture · Seamless switching with effects
Compatibilité	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, s-VHS, component -All currently proposed HDTV extended and improved television standards (1080i, 720p...) -All computer graphics formats from VGA, S-VGA, XGA, S-XGA to U-XGA -Most Macintosh computers -Electronic Workstations with a resolution of up to 1600x1200 at 75Hz -Most sources with a pixel clock up to 160MHz -DVI sources up to SXGA
Communication	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Entrées	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Alimentation CA	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Niveau sonore	
Consommation électrique	Max 620 Watt
Dissipation d'énergie	
Poids	Net weight: Body only 12.9 kg/ 28.5 lbs

Crée le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.