

TransForm NDN-220 Pro

Networked Display Node



Barco's TransForm N Networked Display Node is a powerful PC-based networked graphics processor. It is used in the networked visualization environment of a TransForm N system and can display encoded streams coming from the Gbit Ethernet/IP network. H-264, V2D and ProServer represent just the top of a long list of supported codecs and streaming formats. Furthermore, the display controller also has a high-end graphics card to perform the rendering operations as are requested by the TransForm N management clients in the network.

High density content – Large display walls

The NDN-220 Pro Output nodes can display high density content and can drive up to sixteen HD displays with a single node. The unit supports multiple different types of displays including the whole range of Barco display solutions like RPC, LCD & LED. Managed by CMS inside the TransForm N system multiple NDN-220 Pro output nodes can be combined in a wall-cluster to show a composed synchronized picture on display walls of virtually unlimited size. The NDN-220 Pro offers a dedicated sync-cable based full frame-lock synchronization between up to 30 nodes suiting the needs of video-walls with advanced synchronization requirements.

Features:

- 4 DisplayPort 1.2 outputs
- Up to 4K-UHD resolution per output
- Universal IP video streaming decoding
- Most extensive list of supported codecs and formats

- Network-based content synchronization between multiple display nodes driving a single wall
- Frame lock between multiple display nodes
- Redundant network interface
- Silent operation in a compact and flexible form factor
- Mature Barco quality, robust and reliable
- The NDN-220 Pro has a performance to show up to 12 full HD camera sources per node

Product specifications

TRANSFORM NDN-220 PRO

General specifications

Memory	8 GB
Disk drive	128 GB Solid-State Disk SSD
Network	2x 1Gb/s LAN
Graphics card	Professional high-performance NVIDIA Quadro-series graphic card
Processor	Intel(R) Core(TM) i5-9500E 6-core processor 3.0GHz (4.2GHz max. Turbo frequency)
Output	4x Display Port 1.2 (supporting up to 4x 4K-UHD) 4x DVI-SL via included adapters (supporting up to 4x HD)
Input	H.264, MPEG-2/4, V2D, H.263, VNC, Pro-Server (see supported codec list)
Form factor	3U ½ 19" Rackmount housing
Dimensions	131.5mm x 220mm x 305mm 5.18" x 8.66" x 12.01"
Weight	6.1 kg (7.9 kg incl. packaging)
Power supply	100-240V, 8-4A, 50/60Hz
Power consumption	270 W (max)
Temperature range	0° -40°C 32° -104°F
Humidity	Max. 80% (noncondensing)
Altitude	Up to 5000m (operation)
Noise Level	Max. 35dbA (measured at 1m/32.8ft distance at 22°/72)
Compliance	CE, UKCA, CB/UL 60950/62368-1, ICES, CCC, FCC Class A Regulatory Model Id: P220
Order Information	R9822000 NDN-220 PRO Display Node (no power cable) R9822000B NDN-220 PRO Display Node (US) R9822000D NDN-220 PRO Display Node (IN) R9822000F NDN-220 PRO Display Node (EU) R9822000G NDN-220 PRO Display Node (UK) R9822000I NDN-220 PRO Display Node (CN) R9822000X NDN-220 PRO Display Node (C13/C14 power cable) R9821099 Rackmount kit for 2x NDN-220 PRO/LITE R766042 Pedestal mount kit for NDN-220 PRO/LITE

Last updated: 08 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.