


D310



- -3 to 2 and 2 to 2 Pull Down (patented Motion Picture Processing)-Time Based Correction-Video Equalizing (3-Band)-Dynamic Image Stabilization-Digital Brightness/Saturation Control-Scaler/Compressor-Automatic RGB Matrix Selection-Analytical Contrast Rendering (Stretch to SubBlack, Gamma (RGB))-Luminance Tracking-Dynamic Sample Weight Distribution

Общие характеристики

Совместимость	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43 in Composite, S-VHS, RGB or Component format) -All computer graphics up to SVGA (800 x 600) -All Macintosh computers (640 x 480) -Pannellink loop through data signal
Входы	-Two Composite Video inputs on BNC connectors -Two S-video inputs on 4 pin mini-Din connectors -Once Component Video input (R-Y, B-Y, Y, sync) on 4 x BNC connectors -One RGBs or RGsB input on 4 x BNC connectors -One Pannellink input
Выходы	-Pannellink data output -Long/Short Distance digital link -RGBs or RGsB output on HD15 connector (monitor) -RS 232 loop-through communication port on D9 male & female connectors -RS 485 Phoenix connectors for AX Link

Создано: 09 Jul 2024

© 2024 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.

www.barco.com