

SLM G8 Performer

A compact and Powerful Projector for Rental & Staging Applications



기술 사양

SLM G8 PERFORMER

일반 사양	
광 출력	8,000 ANSI Lumen
해상도	1024 x 768 (native) 1600 x 1200 (max)
해상도	1024 x 768 (native) 1600 x 1200 (max)
Digital MicroMirror Device™	3 high resolution XGA DMD's
밝기 균일도	> 90 % for the total screen area
명암비	Normal mode: 500:1 High mode: 1000:1 (Full White/Full Black)
램프	Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp power: 2,0 kW
소음도(@ 20°C -68°F)	
소음도(@ 40°C -104°F)	
기본 전압	200 -240 V
전력 소비	2,550 W
주위 온도	35°C (95F) max
크기	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
무게(리깅 기어 포함)	57 kg (126 lbs)
렌즈	BARCO's "click-and-play" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
렌즈범위	Motorized V shift: up to 118% Motorized H shift: up to 65%
실드 DLP™ 코어	No
무이음경계선(Seamless) 전환	Standard
ScenergiX	Standard
네트워크 연결	Optional
고정 입력	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input)
옵션형 입력	One free digital input slot for optional input modules: · SDI · HD -SDI
원격 제어	• RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote)

작성일: 15 Mar 2023

기술 사양은 예고 없이 변경될 수 있습니다. 최신 정보는 www.barco.com에서 확인하십시오.

ENABLING BRIGHT OUTCOMES

BARCO