


Galaxy 4K-32 HFR

3D stereo, 33,000 lumens, 4K three-chip DLP projector



With its 4K (4096x2160) resolution and 33,000 lumens light output, Barco's Galaxy 4K-32 projector brings extreme bright high-fidelity 3D imagery to virtual reality installations worldwide.

The Galaxy 4K-32 features patented color convergence technology. In addition to the excellent color saturation of three-chip DLP technology, the projector also ensures solid color and brightness uniformity. For high fidelity 3D applications with full 4K resolution, the Galaxy 4K projector is what you seek.

3D stereo flexibility

Thanks to the projector's 4K resolution, important details are more visible than ever, whether in design models or in layers of geophysical data. With active 3D stereo and optional active Infitec Excellence 3D in its native 4K resolution, you can choose the type of 3D stereo that fits you best. The Galaxy 4K-32 HFR does 120hz stereo based upon frame doubling 2x60hz.

Its New active Infitec Excellence filters offers 40% more stereo lumens and excellent stereo separation between left and right eye content.

In for the long haul

With a sealed optical engine and enhanced display chip cooling, Barco's Galaxy 4K series makes sure its core components don't falter over time. In addition, the Galaxy 4K's modular design ensures quick servicing and increases uptime, and its user-friendly interface makes diagnostic and setup operations a breeze. This includes a choice between direct lamp replacement and full lamp house swaps, depending on your needs.

Product specificaties**GALAXY 4K-32 HFR****General specifications**

Digital MicroMirror Device™	3 x 1.38" DC4K dark metal devices
Native resolutie	4,096 x 2,160 pixels
Behuizing	Hermetically sealed DMDs and optical assembly
Lamp	6.5 kW (Xenon lamp)
Lichtuitvoer	33,000 lumens (Full power)
Schermafmaat	Up to 23m / 75 ft wide
Contrastverhouding	2,000:1
Digitale video-ingangen	2 x DisplayPort 1.1a, 2 x 3G-SDI SMPTE 292/424, HDMI 1.4a on projector 4 x DisplayPorts 1.1a and 4 x 3-pin Mini Din stereo inputs on MCM-400
I/O-controle	Ethernet, 8x GPIO, Serial RS232
Primelenzen	Fixed focal 0.72, 0.9:1 lenses for on-axis usage 1.13 -1.66 zoom lens
Projectordiagnose	via PC touch panel via Communicator control software via SNMP agent
Voedingsvereisten	3W+N+PE 230/400V 16A 50-60Hz or 3W+PE 208V 27A 50-60Hz 30,000 BTU/hr (with 6.5kW lamp)
Afmetingen	604(H) x 754(W) x 1129(D) mm 23.78(H) x 29.69(W) x 44.45(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Gewicht	134 kg (295 lbs)
Omgevingstemperatuur	35°C / 95°F Max.
Luchtuitstroom	350 -390 CFM (10 -11 m³/min)
Standaardkenmerken	Full 4K mono and 120 Hz 4K 3D on-screen active stereo capabilities Frame doubled/Dual Flash 3D: 60hz -> 120Hz 4K 3D Active stereo support CLO (Constant Light Output) Powerful SNMP agent Motorized/memorized lens (focus & shift) HDCP support Advanced patented DMD cooling
Beeldverwerkingsapparaat	MCM-400 HFR is standard offered as package with the projector to further expand input flexibilities and allow multi channel usage.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO