

RDA-144

Re-configurable Distribution Amplifier



기술 사양

RDA-144

일반 사양	
비디오 입력	Number: Supports (4) high-bandwidth video inputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per input channel Video Level: 1.0V p-p (nominal); 2.0V p-p (maximum) Sync Levels: Separate C or H/V, 0.7 to 5V p-p; Sync on Green: -0.3V Impedance: 75 ohms
분배 증폭기 성능	Video Bandwidth: 450 MHz ; 375 MHz in fully bridged 1:16 configuration Gain: Unity
비디오 출력	Number: Supports (16) high-bandwidth video outputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per output channel Video Level: 1.0V p-p (nominal); 2.0V p-p maximum Sync Level: TTL sync, 0-3.5V levels Impedance: 75 ohms Re-configuration Options: ▪ (4) 1:4 distribution amplifiers ▪ (1) 1:8 and (2) 1:4 distribution amplifiers ▪ (2) 1:8 distribution amplifiers ▪ (1) 1:12 and (1) 1:4 distribution amplifiers ▪ (1) 1:16 distribution amplifier
물리적	Chassis: Rugged metal enclosure suitable for table top or rack-mounting Dimensions: 5.25" high x 17" wide x 13" deep Shipping Weight: 22 lbs. Agency Approvals: UL, CSA and CE
입력 전력	110/220 VAC, 50/60 Hz, 75 W maximum
환경	Temperature: 0-40 degrees C Humidity: 0-95%, non-condensing
보증	All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

