

RLM R6+ Performer

<P>SXGA+, 6,000 lumens three-chip DLP projector</P>



Technische Daten**RLM R6+ PERFORMER****Allgemeine technische Daten**

Lichtausgabe	6500 Center lumen 6000 ANSI Lumen
Auflösung	1400 x 1050 (native)
Helligkeitsgleichförmigkeit	> 90% for the total screen
Kontrast	1600:1 (full field)
Display	3 Chip DLP SXGA+ (resolution of 1400 x 1050 pixels (aspect ratio 4:3)).
Konvergenz	Max allowed convergence drift is 0.5 pixel. This is checked on vertical and horizontal midlines only. Corners are not applicable for convergence error. This is measure with TLD 1.2 lens on axis.
Merkmale	<ul style="list-style-type: none">■ Autolmage■ Advanced picture-in-picture■ Seamless switching with effects■ Standard light shutter■ Advanced digital zoom■ Rigging point■ Carrying handle■ Frame■ P7 color processing
Bild-im-Bild	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Eingänge	Fixed inputs <ul style="list-style-type: none">■ 1x Configurable 5-Wire (BNC)■ 1x Composite Video (BNC)■ 1x S-Video (4-pin mini-DIN)■ 1x analogue RGB (D15 connector)■ 1x SDI/HDSDI (+ loop through)■ 1x DVI (Digital Visual Interface)
Ausgänge	HDSDI/ SDI loop out
Kommunikation	<ul style="list-style-type: none">■ 1x RS-232C IN (D-9 connector)■ 1x RS-232C OUT (D-9 connector)■ 1x RS-232C IN (XLR connector)■ mini-jack for wired remote control
Kompatibilität	<ul style="list-style-type: none">■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats■ All currently proposed HDTV, extended and improved television standards (1080i, 720p)■ All computer graphics formats from VGA, SVGA, XGA, SXGA,full HD to UXGA■ Most Macintosh computers■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz■ Most computer sources with a pixel clock up to 200 MHz■ DVI sources up to SXGA+
Eingangsquellenkompatibilität	1600 x 1200 (max. input)
Bildgröße	From 1-7m / 3-23ft.recomended
Frequenzen	Pixel clock >162Mhz (UXGA 60hz)
Netzwerk-Verbindung	Optional (10 base-T)
Umgebungstemperatur	Max 40°C (104°F)
Lampe	2 x 250 W mercury Lamp warranty: 1000 hrs

Technische Daten**RLM R6+ PERFORMER**

Optiken	Lens	Order Nr
	TLD (HB) 0.8	R9842040
	TLD (HB) 1.6 - 2.0	R9842060
	TLD (HB) 2.0 - 2.8	R9842080
	TLD (HB) 2.8 - 5.0	R9842100
	TLD (HB) 5.0 - 8.0	R9842120
Lens Shift	Vertical: -10% to +110% Horizontal: -50% to +50% (small differences occur per lens type)	
Objektiv-Encoder	On zoom and focus (with TLD lenses)	
ScenergiX	Standard horizontal and vertical electronic edge blending	
Gekapseltes optisches System	Standard	
Staubfilter	Metal filters	
Geräuschpegel	42 dB(A) (at 40°C)	
Netzspannung	92-240 V / 50 -60 Hz	
Stromverbrauch	700 W	
Wärmeabgabe	Max 2217 BTU/h	
Stromversorgung	90V -255V (50 Hz -60Hz)	
Gewicht	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)	
Abmessungen	W x L x H 705 x 707,8 x 316,5 mm (27.8 x 27.9 x 12.5 inch)	
Verpackungs-Abmessungen	Width: 56 cm Height: 100 cm Depth: 100 cm Floor Space: 1 m ² Volume: 0,56 m ³ Gross Weight: 65 kg	
Sicherheitsstandards	Compliant with UL1950 and EN60950	
Elektromagnetische Interferenz	Complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A	
Bestell-Information	Projector body (without lens): R9010270 Spare dual lamp: R9852940	

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.