

OLite 612 Fixed

Small pitch, surface-mounted creative LED tile



WIDE VIEW

12mm

PIXEL PITCH

IP65

WATERPROOF



Product specificaties**OLITE 612 FIXED****General specifications**

Pixelpitch	12.4 mm
Helderheid	6,000 nits
Led-configuratie	3-in-1 SMD
Pixeldichtheid	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
Pixeldichtheid	3,888 LEDs per tile (72x54) (rental) 1,944 LEDs tile (36x54) (fixed)
Hor. kijkhoek	110° (min 50% brightness)
Vert. kijkhoek	+40, -50° (min 50% brightness)
Contrastverhouding	1,150:1 (at 500 lux)
Levensduur	50,000 hours to 50% of initial brightness
Energieverbruik	800W/tile (max) -240W average (rental) 400W/tile (max) -120W average (fixed)
Netspanning bij gebruik	200-240V / 50-60Hz
Paneelafmetingen	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
Paneelafmetingen	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
Paneelafmetingen	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
Paneelafmetingen	Width: 896mm (rental) Height: 672mm (rental) Depth: 246mm (rental) Width: 448mm (fixed) Height: 672mm (fixed) Depth: 116mm (fixed)
Gewicht / tegel	58 kg (rental) 17 kg (fixed)
IP-classificatie	IP65/65
Verwerking	16 bit/color
Kleuren	281 trillion
Vernieuwingsnelheid	800Hz
Opbouw voet	Max. 12 tiles high
Opbouw truss	Max. 15 tiles high
Link-interface	DVI interface (DVI connector)
Max. lengte link	4.5m (with Barco DVI cable)
Interfaces	2x DVI link
Max. stroomcascadeschakeling	3 tiles
Onderhoudsgemak	Back
Bedrijfstemperatuur	-20 -45°C
Opslagtemperatuur	-20 -60°C
Operationele vochtigheid	10-99%
Vochtigheid bij opslag	10-99%
Broncompatibiliteit	CVBS, YC, YUV, RGB, DVI, SDI, HDSDI (DX700: and Dual link DVI, Dual link HDSDI)
Bedienbare digitizer	DX-700 (with DVI output card), D320, LED-PRO
Certificeringen	UL, CE class A, TUV, FCC, ClassA

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.