

# F50 WQXGA

Compact 120 Hz, single-chip DLP projector with WQXGA resolution



- **Razor-sharp images with vivid colors**
- **Active 3D stereo and high frame rates**
- **Compact and rugged design**

The Barco F50 is the world's first lamp-based single-chip DLP® projector that combines native WQXGA (2,560 x 1,600) resolution with active 3D stereo and high frame rates. Designed for 24/7 operation, the F50's total cost of ownership is reduced to a minimum thanks to its reliable DLP® technology, filter-free design, and low maintenance needs. The compact F50 projector is suited for a wide variety of demanding applications in virtual reality, simulation and training, visitor attractions, collaboration suites and scientific visualization.

## **Unmatched image quality**

With its cutting-edge optics that deliver razor-sharp images, the F50 displays flawless images with vivid colors, and rich in contrast. Producing low noise levels, it also features RealColor™ color management, Smear Reduction Processing™ and high frame rates. The F50 boasts four different digital input sources and a wide range of expansion modules and high-quality projection lenses.

## **Key benefits**

- Small, compact and ruggedized
- Ultimate reliability and low TCO
- Low operational noise level
- Active 3D stereo
- Smear Reduction Processing™/ 120Hz Refresh Rates / High Frame Rates

**Product specifications****F50 WQXGA**

General specifications	
Projector type	Single chip DLP digital projector
Technology	LVDS DMD™ with DarkChip3™
Resolution	2,560 x 1,600
Brightness	5,000 ANSI lumens (High Brightness) 2,500 ANSI lumens (VizSim Bright) 1,800 ANSI lumens (VizSim)
Contrast ratio	up to 5,300:1
Brightness uniformity	>80%
Aspect ratio	16:10
Lens type	All pure glass lenses
Lenses	Ultra Wide Fixed EN53 (0.79:1 @1.65m) Wide Fixed EN52 (0.99:1) Super Wide Zoom EN55 (0.86 -1.16:1) Wide Zoom EN56 (1.14 -1.74:1) Zoom EN51 (1.71-2.37:1) Ultra short throw EN57 (0.3:1)
Optical lens shift	Vertical up to 142%, depending on lens Horizontal up to 64%, depending on lens Motorized lens shift
Color correction	RealColor™
Lamps	1 x 350W UHP (dimmable)
Lamp lifetime	Up to 2,000 hours (Full power), Up to 2,500 hours (Eco mode)
Lamp house, quick replace	Yes
Lamp warranty	500 hours or 90 days
Sealed DLP™ core	Yes
Orientation	Table -ceiling (360 degrees through lamp axis)
3D	Up to 2,560 x 1,600 @ 120Hz
Inputs	2x DisplayPort 1.2 (HBR2), 1 x DVI-Dual Link, 1 x HDMI 1.4a, 1 x VGA, 2x 3G-SDI, 1x HDBaseT
Input resolutions	2,560 x 1,600 -640 x 480 pixel resolution, RGBHV, RGBS, RGsB, custom formats available, HDTV (1080p, 1080i, 720p), NTSC, PAL, SECAM
Max. pixel clock	Up to 600 Mhz (2,560 x 1,600@120 Hz max) DP 1.2 Up to 330 Mhz Dual link DVI
Software tools	SimCAD, Projector Toolset
Control	IR, RS232, Ethernet, USBA, 2x BNC sync, 1x MiniDIN
Network connection	10/100/1000 base-T, RJ-45 connection, RS-232
Power requirements	100-240V 50-60Hz
Power consumption	less than 530W
Operational ambient temperature	10 -40 °C /50 -104 °F, 0-3,000m (Storage temperature: -20 -60 °C/-4 -140 °F)
Operating humidity	20 -80% RH (Storage Conditions: 10 -90% RH)
Dissipation BTU	max 1,807 BTU/h
Dimensions (WxLxH)	342 x 306 x 143 mm / 13.46 x 12.05 x 5.63 in
Weight	7.5 kg / 16.5 lbs
Standard accessories	Power cord, wireless remote control
Certifications	Compliant with FCC, part 15 Class A and CCC, cNus, cUL, UL and CE
Warranty	Limited 3 years parts and labour

Last updated: 16 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.