


Wodan

Designed for larger screens, Wodan delivers unbelievably bright and detailed images with spectacular color fidelity.



- Theater & Media Room Series
- 4K UHD Resolution (3,840 x 2,160)
- 3-Chip DLP
- Up to 15,000 ANSI Lumens

Wodan builds on the successful platform the Apollo 20. Designed for large screens, bright ambient light environments, outdoor entertainment spaces and contemporary glass home designs, each can benefit from an unbelievably bright and detailed image with spectacular color fidelity. What's new? Wodan has completely new processing electronics, connectivity and even more powerful built-in warp. Wodan features motorized lenses and lumen output is variable from 8,000 to 15,000 lumens.

Single Step Processing SSP™

Pulse is a hardware and software based platform that simplifies the signal allowing it to transmit from source to screen much faster, more efficiently and with less artifacts than ever before. We use an advanced image processing technique to display the image on the screen without any artefacts and with the lowest possible processing lag, this is made possible by our Single Step Processing (SSP™).

State of the art electronics

All new Pulse electronics have been designed to process 4K with HDMI 2.0a and HDCP 2.2 and the optical engine is utilising the very latest 0.9" DMD DLP chipset, delivering 3,840 x 2,160 pixels on screen. Wodan also features HDR, motorised lenses and auto aspect detection between 16:9 and cinemascope formats. Featuring Barco's unique RealColor processing, Wodan enables simple and accurate calibration to any desired white point or greyscale.

Building Blocks

Wodan offers 4K UHD resolution for superb image quality. Currently the most compact projector that offers 15,000 lumens light output, one of its most striking features is light-on-demand, offering flexible light output for different installation requirements.

Technische Daten

WODAN

Allgemeine technische Daten

Projektortyp	Three chip DLP
Technologie	3 x 0.90" DMD™
Auflösung	3,840 x 2,160 (4K UHD)
Bildseitenverhältnis	1.78:1 (16:9)
Lichtquelle	2.5 kW Xenon Lamp
Lebensdauer der Lichtquelle	1,000 hours typical
Lichtausgabe	Up to 15,000 ANSI lumens
CLO (Constant Light Output - Konstante Lichtausgabe)	Yes
Kontrast	2,200:1 Sequential 450:1 ANSI
Helligkeitsgleichförmigkeit	90%
Objektivbereich	TLD+ (0.43:1) TLD+ (0.73 - 0.94:1) TLD+ (0.92 - 1.33:1) TLD+ (1.24 - 1.56:1) TLD+ (1.48 - 2.00:1) TLD+ (1.99 - 2.76:1) TLD+ (2.73 - 4.43:1) TLD+ (4.50 - 7.50:1) TLD+ (7.40 - 11.00:1)
Linsenverstellung	Up to 65% vertical lens shift & up to 20% horizontal lens shift (depending on lens selection) Motorized zoom, focus, shutter and lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information
Optischer Dowser	Yes
Farbkorrektur	P7 RealColor™
Farbskala	Up to DCI (P3)
Bildverarbeitung	Embedded warp, bow correction & blend engine
WARP	Four corner warp
Ausrichtung	Table / Ceiling / Portrait (Lamp door down facing -see installation manual notes) / Vertical
Netzwerk-Verbindung	10/100 Ethernet via RJ45 connection
Integrierter Webserver	Yes
HDR	HDR10
3D	Active Eyewear (optional) Passive Infitec (optional) Passive Circular (optional) Double flash up to 96Hz Additional hardware required please contact an authorized Barco representative for details
Eingänge	1 x HDMI 2.0a (HDCP 2.0), 2 x HDBaseT (HDCP 1.4), 1 x Display Port 1.2 Quad 3G/12G SDI/BarcoLink
Eingangsaufösungen	VGA up to 4K (4,096 x 2,160) @ 120Hz
Bedienung	IR, RS232, TCP/IP, WiFi (Optional), XLR Wired Remote, GSM (Optional), DMX 512 Driver modules available for: Crestron, Control4 and Savant
Stromversorgungsanforderungen	110-130V / 200-240V / 50-60 Hz
Stromverbrauch	3,000 W / STBY
Geräuscentwicklung (typisch bei 25 °C/77 °F)	53 dB(A)
Betriebstemperatur	0 to 40°C (sea level)
Betriebsfeuchtigkeit	0 to 80% (relative humidity)
BTU pro Stunde	Max. 5,800 BTU/h @ (110-130V) Max. 10,236 BTU/h @ (200-240V)
Anforderungen Luftstrom	Air Inlet (from Rear w/Feet Down): Front Exhaust (from Rear w/Feet Down): Rear
Abgasstrom	TBD
Abmessungen (BxTxH)	475 x 725 x 382 mm (excluding lens) 18.70 x 28.54 x 14.96 in. (excluding lens)
Gewicht	50kg / 110lbs (excluding lens)
Versandabmessungen (BxLxH)	650 x 900 x 560 mm (excluding lens - packaged separately) 25.59 x 35.43 x 22.04 in. (excluding lens - packaged separately)
Versandgewicht	TBD (excluding lens - packaged separately)
Lagerungstemperatur	TBD
Luftfeuchtigkeit bei Lagerung	10 to 90% (relative humidity)
Standardzubehör	Power cord(s), wireless / XLR wired remote control
Zertifizierungen	Compliant with UL60950-1 and EN60950-1, complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS
Gewährleistung	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.

www.barco.com

