

Acsar

D-Cine Alternative Content Switcher and Router



Technische Daten

ACSAR

Allgemeine technische Daten

Video-Eingänge	Modules: hot plugable slots: x8 on back panel, each accepting the following input modules -analogue RGBHV, Analogue RGB, Composite Sync, Analog RGB sync on green -SDI -HD SDI -Analog composite video and S-video with digital decoder
Interne Verarbeitung	10 bit
Video-Ausgänge	DVI: 1 Digital Versatile Interface standard output at 1280x1024, 50/60 Hz
Kommunikation	In/Out: 2x D9 RS 232 connectors
Netzwerkfähigkeit	Via an optional single board computer with remote network management
Bedienfeld	Source selection: via a selection wheel; turn to select/push to activate. Display: Four line LCD display of 40 characters for menu scrolling & source selection. Power Switch: On/Off
Stromversorgung	Built-in power supply 85-253V auto-ranging Mains frequency: 50/60 Hz
Stromverbrauch	200 W
Fernbedienung	Barco RC5 remote control
Größe	Processor: 19" rack (w) x 4u (h) x 400 (d) mm with input modules Optional video input patch panel, 19" rack x 1u (h)
Gewicht	Processor only: 10.3 kg/22.7 lbs Fully loaded: appr. 16.4 kg/36.2 lbs depending on input module configuration

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.