


# OverView LVD-5521D

55" extreme narrow bezel (ENB) LCD video wall for entry level and mid-end applications



- 500 Nit brightness, ENB generation
- Superb inter-tile color and brightness
- User-friendly video-wall setup and control interface
- Sense X brightness and color automatic calibration with integrated sensors
- Fan-less solution for noiseless performance
- Reduced energy consumption
- Optional 5-year service packages

Barco's OverView LVD-5521D is a high-performance, mid-level brightness (500 cd/m<sup>2</sup> typical) and cost optimized 55" LCD-panel, dedicated for use in tiled video wall applications. Being part of the ENB 1.8 mm bezel generation, with excellent colors and a wide viewing angle, the OverView LVD-5521D provides great value to entry level and mid-end applications.

### A perfect image with automatic calibration

The OverView LVD-5521D is part of Barco's highly renowned and industry-leading OverView LCD video wall portfolio -which complements the premium Barco UniSee platform. The signature innovative Sense X -Barco's automatic real-time calibration system -ensures that the complete wall produces a perfectly balanced image at all times -thus avoiding a video wall with a 'checkerboard' pattern image. Barco is the only company in the market enabling this type of automatic calibration in real-time based on integrated brightness and color sensors.

### Enhanced uptime, reduced power consumption

The use of Barco's Video wall Manager makes it much easier to control the video wall, further improving the user-friendliness.

**Product specifications****OVERVIEW LVD-5521D**

<b>Panel</b>	
Technologia LCD	In-plane switching
Rezolucja	Full HD (1920 x 1080 pixels)
Podświetlenie	Direct LED
Format obrazu	16:9
Jasność	500 cd/m <sup>2</sup> (typ.)
Kontrast	1200:1 (typ.)
Punkt bieli	Native 10000 K (typ.)
Kalibrowanie	Sense X automatic color and brightness calibration
Żywotność podświetlenia	60000 h (typ.)
Chłodzenie	Fan-less
Zamglenie ekranu	25%
Temperatura robocza	0°C -40°C
Wilgotność operacyjna	10% -80% non-condensing
Temperatura przechowywania	-20°C -60°C
Wilgotność przechowywania	5% -90% non-condensing
Montowanie	VESA 600 x 400
<b>Zasilanie</b>	
Napięcie wejściowe prądu przemiennego	100 -240 VAC, 50 -60 Hz
Pobór energii	170 W (500 Nit native)
Rozpraszanie ciepła	580 BTU/h
<b>Wymiary</b>	
Wymiary	1211.5 x 122.1 x 682.3 mm   47.69" x 4.08" x 26.86"
Aktywna przekłtna ekranu	55" (1397 mm)
Aktywny obszar ekranu	1209.6 mm x 680.4 mm   47.62" x 26.79"
Waga	27.55 kg   60.74 lbs
Generowanie szerokości ramki	ENB (1.8 m   0.07") generation
<b>Porty</b>	
DisplayPort	2x DP1.2 inputs (DisplayPort 1.2 cables must be used when the cable length exceeds 3m / 10 ft) 1x DP 1.2 output
HDMI(TM)	2x HDMI™ 2.0 inputs
Port Ethernet	1
USB	1 input (only for power)
HDCP	Yes (HDCP 2.2)
<b>Model</b>	
Nazwa modelu	OverView LVD-5521D
<b>Inne</b>	
Numer artykułu	R9867810

Last updated: 19 Sep 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.