

RDA-144

Re-configurable Distribution Amplifier



技术规格

RDA-144

一般规格

视频输入	Number: Supports (4) high-bandwidth video inputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per input channel Video Level: 1.0V p-p (nominal); 2.0V p-p (maximum) Sync Levels: Separate C or H/V, 0.7 to 5V p-p; Sync on Green: -0.3V Impedance: 75 ohms
配电放大器性能	Video Bandwidth: 450 MHz ; 375 MHz in fully bridged 1:16 configuration Gain: Unity
视频输出	Number: Supports (16) high-bandwidth video outputs Video Type: RGBHV, RGBS, RGsB, RsGsBs, Component, S-Video, Composite Connectors: (5) BNC connectors per output channel Video Level: 1.0V p-p (nominal); 2.0V p-p maximum Sync Level: TTL sync, 0-3.5V levels Impedance: 75 ohms Re-configuration Options: <ul style="list-style-type: none">▪ (4) 1:4 distribution amplifiers▪ (1) 1:8 and (2) 1:4 distribution amplifiers▪ (2) 1:8 distribution amplifiers▪ (1) 1:12 and (1) 1:4 distribution amplifiers▪ (1) 1:16 distribution amplifier
物理的	Chassis: Rugged metal enclosure suitable for table top or rack-mounting Dimensions: 5.25" high x 17" wide x 13" deep Shipping Weight: 22 lbs. Agency Approvals: UL, CSA and CE
输入电源	110/220 VAC, 50/60 Hz, 75 W maximum
环境	Temperature: 0-40 degrees C Humidity: 0-95%, non-condensing
保修期	All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。