

NGS-D320 FLEX

Compact 4K single channel H.264 & V2D Encoder



- **Superb Visual Experience**
- **Simple Integration**
- **No Adjustment Needed**
- **Performance**
- **Flexible switching between the H264 or V2D protocol**
- **Part of the TFN and OpSpace Product families**

The NGS-D320 FLEX is a versatile and powerful networked H.264 and V2D encoder. Its elegant design, small form factor and silent operation allows the device to be used in any situation, both in office environments and in 24/7 mission critical applications.

Due to its versatility, the NGS-D320 FLEX can be configured at runtime as an encoder, both for DVI, HDMI™ and DisplayPort content, with or without audio and USB KB/M. Unique in the market, it supports 2 types of streaming protocols (H264 and V2D) in a flexible way, enabling the best possible user experience for a wide variety of use-cases. The combination of these functions, with integrated keyboard and mouse control in a single unit, is ideal to create a seamless environment for application sharing, simulation and training.

Key features:

- **Superb Visual Experience**The NGS-D320 FLEX comes with Barco's latest image processing engine, which provides the best scaling and color space conversion algorithms on the market today. When distributing graphics, the encoder preserves even the smallest details, making it suitable to encode images like spreadsheets or single pixel line diagrams.
- **Simple Integration**The device automatically starts streaming whenever a valid input signal is connected. The stream is automatically set up using the most optimal settings based on input resolution and bandwidth. In addition, the discovery page of the web interface gives an overview of all available devices in the network, making system configuration easy. The device is validated to work in Barco Transform N 3.3 or higher and OpSpace 1.4 or higher.
- **No Adjustment Needed**With automatic EDID management, the best experience in distributing graphics and video over IP is guaranteed.
- **Performance**The NGS-D320 FLEX comes with a dual link DVI, an HDMI™ 1.4 and a DisplayPort 1.1a input. All inputs support resolutions up to 4096 x 2160 (DCI) and feature active pass-through connectivity. Encoding in full frame rate or lower frame rates are possible, allowing you to define the quality/bandwidth balance. The encoder latency is below 40ms enabling the foundation for a low end-to-end latency in a broad variety of systems.

Product specificaties**NGS-D320 FLEX**

| Number of inputs and outputs | |
|------------------------------|--|
| Audio | 1 3.5mm jack stereo line level in & line out 1 3.5mm jack mono mic in & stereo headphones out (combined) |
| USB | 3 Type A connectors, 1 Micro-B connector |
| Netwerk | RJ45 (1Gb copper) |
| Video | 1 Dual Link DVI & 1 DisplayPort 1.1a & 1 HDMI 1.4 input 1 Dual Link DVI & 1 DisplayPort 1.2 & 1 HDMI 1.4 output Flexible Loop Through Maximum input bandwidth of 330Mhz |
| Network interfaces | |
| Ethernet | 2x 1GbE full duplex |
| IP-adressering | DHCP, link local, fixed IP |
| Protocollen | Unicast, Multicast (IGMP v3), RTP, RTSP, DNS, NTP |
| RTSP-sessies | Multicast: maximum 12 simultaneous RTSP session per channel Unicast : maximum 2 simultaneous RTSP session per channel |
| Detectie | Zeroconf, SAP (RFC 2974) |
| Management interfaces | |
| Firmware-upgrade | HTTPS Web interface, USB Storage Device |
| Alleenstaand | HTTPS Web interface |
| Advanced features | |
| Beeldverwerking | Color space conversion, scaling, frame rate reduction |
| Automatische verkleining | Y (Adjust to profile) |
| Extern toetsenbord en muis | Supported (Native keymap) |
| General specifications | |
| Afmetingen | 38 mm H x 170 mm W x 170 mm D 1.5" H x 6.7" W x 6.7" (+/-2mm / 0.1") |
| Gewicht | 1 ± 0.01 kg (2.20 lbs) |
| Vermogen | Typical 35W, maximum 48W |
| Voeding | 12VDC, 100-240VAC 60W, external locking power |
| Bedrijfstemperatuur | 0°C to 40°C (32°F to 104°F) |
| Opslagtemperatuur | -20°C to 70°C (-4°F to 158°F) |
| Geluidsniveau | Typical 32dBA at 20°C |
| Montage | Optional VESA adapter plate or 1U rack mount for 2 devices |

Product specificaties**NGS-D320 FLEX**

| Certification | |
|-------------------------------------|---|
| EMC | CE, FCC Part 15 Class A, ICES-003 |
| Veiligheid | UL/ cUL/ EN/ IEC 60950-1 CB report |
| Wettelijke naam | NGS-D320 |
| Packaging characteristics | |
| Afmetingen (verpakt) | 382mmx273mmx85mm 15,04"x10,75"x3,35" |
| Gewicht (verpakt) | 2.2 kg 4.8 lbs |
| NGS-D320 Flex | |
| Aantal kanalen | 1 |
| Aantal streams | 1 |
| Grafisch | 640x480 -2560x1600 24-60Hz 640x480 -4096x2160 24-30Hz |
| Audio | 16bit 48kHz stereo |
| Codec | Video: H.264 up to level 5.0 or V2D -60fps: up to 1920x1200 (1x) -30fps: up to 2560x1600 (1x) -15fps: up to 4096x2160 (1x) |
| Bandbreedte | Video: H.264 384kbps – 12 Mbps V2D 25Mbps – 100Mbps Audio: uncompressed |
| Latentie encoder-decoder end-to-end | 80-200ms (typical 100ms) |
| Opstarttijd | 15s |

Laatst bijgewerkt: 16 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.