

G100 rigging frame

Rigging frame for the G100 series



Rigging frame for the G100 series (*)

(*) When the UST lens (R9802360) is combined with the G100 rigging frame (R9802681), a minimum lens shift is required to avoid shadows. Relative to the center position the lens needs to be shifted upwards by a minimum of 8%, and to the right by a minimum of 21% (100% = half the image height/width). The removable front bar of the frame should also be removed.

It's not recommend to use the G100 rigging frame when building a dual stacked setup using the UST lens

Product specificaties**G100 RIGGING FRAME****Algemene specificaties**

Size	88.7 x 78.3 x 43.3 cm / 34.9 x 30.8 x 17.1 in
Weight	25.4 kg / 56 lbs

Laatst bijgewerkt: 28 Apr 2025

© 2025 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO