

ScreenPRO

ScreenPro™ is ideal for use whenever multiple video sources must be seamlessly switched to provide a professional quality presentation; staging events, auditoriums, multimedia presentations, educational and training events.



技术规格

SCREENPRO

一般规格

视频输入	<p>Universal A/V Inputs: (8) high bandwidth video channels High-Resolution Video: Supports conversion of RGB videos with horizontal scan rates up to 100 KHz and resolutions up to 1600x1200. HDTV 480p, 720p, and 1080i formats are supported in RGB colorspace. Input levels are independently programmable.</p> <p>Standard Video: Accepts RGB, Y Pb Pr, S-Video (Y/C), or NTSC/PAL video formats. Input levels are independently programmable for RGB and Y Pb Pr sources. Programmable luminance and chrominance levels are provided for S Video, and Hue and Saturation controls are provided for NTSC/PAL inputs.</p> <p>Synchronization: The unit automatically locks to the incoming video source.</p> <p>Input Sync Signals: Sync-on-Video; Separate C or H/V</p> <p>Connectors: BNC</p>
视频输出	<p>High-Resolution RGB Video: User programmable output formats; VGA (640x480), SVGA (800x600), XGA(1024x768), SXGA (1280x1024), For plasma displays, 832x624, 848x480, 852x480, 1280x768, 1365x768, 1365x1024. Also provides HDTV 480p and 720p output rates.</p> <p>Main Outputs: Two independently buffered channels: (1) RGBHV with five BNC connectors; (1) RGBHV with HD-15 connector.</p> <p>Preview Output: (1) RGBHV with HD-15 connector</p> <p>Output Sync Type: Separate C or H/V</p>
混合和过渡效果	<p>The unit supports seamless switching between sources, including the following transition effects: cut, dissolve, wipe. Transition times and wipe direction are fully programmable.</p> <p>Picture-in-Picture: Supports display of two independently scaled windows.</p> <p>Luminance Keying: Supports image overlay features with useradjustable luminance key levels</p>
用户控制	<p>Source Selection: (9) illuminated keys support selection of 8 video inputs or black screen</p> <p>Transition Effects: (3) illuminated keys: wipe, dissolve, and cut</p> <p>Program Keys: (5) illuminated keys support generation, storage, recall, and editing of preprogrammed control sequences.</p> <p>Freeze Key: A single illuminated key used to freeze the image on the main output.</p> <p>Set-up Controls: Electro-luminescent display, control knob, and 8 keys provide a menu-based front panel interface to simplify set-up.</p>
远程控制	<p>Reconfigurable RS-232/485 port for real-time control; Optional external Ethernet (with TCP/IP and FTP) supports advanced real-time control.</p>
物理的	<p>Height: 5.25" (13.3 cm)</p> <p>Width: 17" (43.2 cm) or 19" (48.3 cm) with rear rack-mount option</p> <p>Depth: 13" (33 cm); Weight: 22 lbs (10 kg)</p> <p>Shipping Weight: 30 lbs (13.6 kg).</p>
输入电源	<p>47-250 VAC, 50-60 Hz, 175 W max</p>
环境	<p>Temperature: 0-40 degrees C; Humidity: 0-95% noncondensing.</p>
保修期	<p>All video products are designed and tested to the highest quality standards and are backed by a full three-year parts and labor warranty.</p>

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。