

Short tele zoom EN24



Focus range: 5.0 - 20.0 m

- SX+ 2.78-4.45:1
- 1080 / WUXGA 2.50-4.00:1

Product specifications**SHORT TELE ZOOM EN24**

General specifications	
Working F/#	F 2.6-3.13 Voice coil operated Iris F 2.5-7.0
Zoom ratio	1.6 Motorized zoom and focus
Focal length	53.3-85.3 mm
Focus Range	Standard: 5m – 20m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.9 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ SXGA+ 2.78-4.45:1■ 1080p/WUXGA 2.5-4.0:1
	Image size tolerance +/-5%

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.